

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2009150003](#)
Status: **Active**
Overview: [MultiCat Power Connectors with Precision-Machined Contacts](#)
Description: [MultiCat High-Power Circular Receptacle Housing, 3 Circuits, Black](#)

Documents:

Drawing (PDF)	Test Summary 2009140003-TS-000 (PDF)
Product Specification 2009140003-000 (PDF)	Datasheet (PDF)
Application Specification 2009140003-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification 2009150003-PK (PDF)	

Agency Certification

UL E29179

General

Product Family	Crimp Housings
Series	200915
Application	Power, Wire-to-Wire
Overview	MultiCat Power Connectors with Precision-Machined Contacts
Product Name	MultiCat
UPC	889056746861

Physical

Circuits (maximum)	3
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PEI
Net Weight	1.963/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.83mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +150°C

Material Info

Engineering Number FKB3W3S

Reference - Drawing Numbers

Application Specification	2009140003-AS-000
Packaging Specification	2009150003-PK
Product Specification	2009140003-000
Sales Drawing	2009150003-000
Test Summary	2009140003-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[200915](#) Series

Mates With

MultiCat High-Power Circular Plug Housing
[2009140003](#)

Use With

MultiCat High-Power Contacts [201846](#) .
MultiCat Female High-Power Pre-Crimped
Lead [797582065](#) , [797582066](#) , [797582067](#) ,
[797582068](#) , [797582069](#) , [797582070](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[200915-0003](#)