

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2018460040

Status:

Active

Overview:

MultiCat Power Connectors with Precision-Machined Contacts

Description:

MultiCat High-Power Receptacle Terminal, Gold over Nickel Phosphorus Plating, 8-10 AWG



Documents:

Drawing (PDF)

Product Specification 2018400000-PS-000 (PDF)

Application Specification 2018400000-AS-000 (PDF)

Packaging Specification 2018460001-PK (PDF)

Test Summary 2018400000-TS-000 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	201846
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	MultiCat Power Connectors with Precision-Machined Contacts
Product Name	MultiCat
UPC	889056747479
Physical	
Durability (mating cycles max)	500
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Nickel Phosphorus
Material - Plating Termination	Gold
Net Weight	2.263/g
Packaging Type	Bag
Plating min - Mating	0.100µm
Plating min - Termination	0.200µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	4.03mm-5.84mm
Wire Size AWG	10, 8
Wire Size mm²	5.26-8.36
Electrical	
Current - Maximum per Contact	40.0A
Voltage - Maximum	1000V AC
Material Info	
Engineering Number	FPG003S204
Reference - Drawing Numbers	
Application Specification	2018400000-AS-000
Packaging Specification	2018460001-PK
Product Specification	2018400000-PS-000
Sales Drawing	2018460040-000
Test Summary	2018400000-TS-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2021)4569-DC (8 July 2021)	
Lead	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

201846 Series

Use With

MultiCat High-Power Inline Receptacle Housing 201841

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for MultiCat Machined High-Power Contact, 8-18 AWG	2002182300
Extraction Tool for MultiCat High-Power Crimp Terminals, 8-18 AWG	2002220200

This document was generated on 09/03/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[201846-0040](#)