

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [2064621100](#)  
**Status:** **Active**  
**Overview:** [Micro-Fit+ Connector System](#)  
**Description:** Micro-Fit+ Terminal Position Assurance (TPA) Retainer, 11 Circuits, 3.00mm Pitch, UL 94V-0, Glow-Wire Capable, Natural

|                                                               |                                                                 |
|---------------------------------------------------------------|-----------------------------------------------------------------|
| <b>Documents:</b>                                             |                                                                 |
| <a href="#">3D Model</a>                                      | <a href="#">Packaging Specification 2064620000-PK-000 (PDF)</a> |
| <a href="#">3D Model (PDF)</a>                                | <a href="#">Test Summary 2064600000-TS-000 (PDF)</a>            |
| <a href="#">Drawing (PDF)</a>                                 | <a href="#">Datasheet (PDF)</a>                                 |
| <a href="#">Product Specification 2064600000-PS-000 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>            |

**Agency Certification**  
UL E29179

|                |                                             |
|----------------|---------------------------------------------|
| <b>General</b> |                                             |
| Product Family | Accessories                                 |
| Series         | <a href="#">206462</a>                      |
| Component Type | Terminal Position Assurance                 |
| Overview       | <a href="#">Micro-Fit+ Connector System</a> |
| Product Name   | Micro-Fit+                                  |
| UPC            | 191130009152                                |

|                               |                |
|-------------------------------|----------------|
| <b>Physical</b>               |                |
| Circuits (Loaded)             | 11             |
| Circuits (maximum)            | 11             |
| Color - Resin                 | Natural        |
| Lock to Mating Part           | Yes            |
| Material - Resin              | Nylon          |
| Net Weight                    | 0.202/g        |
| Number of Rows                | 1              |
| Packaging Type                | Bag            |
| Temperature Range - Operating | -40° to +105°C |

**Material Info**

|                                    |                   |
|------------------------------------|-------------------|
| <b>Reference - Drawing Numbers</b> |                   |
| Packaging Specification            | 2064620000-PK-000 |
| Product Specification              | 2064600000-PS-000 |
| Sales Drawing                      | 2064620000-SD-000 |
| Test Summary                       | 2064600000-TS-000 |



Series image - Reference only

**EU ELV**  
**Not Relevant**

|                                                                                                                                                                                                                                                      |                                                                                                                              |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| <b>EU RoHS</b><br><b>Compliant</b><br><b>REACH SVHC</b><br>Not Contained Per -<br>D(2021)4569-DC (8<br>July 2021)<br><b>Halogen-Free</b><br><b>Status</b><br><b>Not Low-Halogen</b><br>For more information, please visit <a href="#">Contact US</a> | <b>China RoHS</b><br><br><br><br><br><br><br><br>China ROHS Green Image<br>ELV Not Relevant<br>RoHS Phthalates Not Contained |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|

**Search Parts in this Series**  
[206462](#) Series

**Use With**  
Micro-Fit+ Receptacle Housing [206461](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[206462-1100](#)