

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2451350820

Status:

Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit Jr.-to-Mini-Fit Jr. Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 2.0m Length, 8 Circuits, Black



Series image - Reference only

Documents:	
3D Model	Packaging Specification 2027040005-PK (PDF)
3D Model (PDF)	Datasheet (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	245135
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mini-Fit Jr. Both Ends
Overmolded	Yes
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Jr.
Type	Overmolded Assembly
UPC	889056879637
Physical	
Cable Length	2.0m
Circuits (Loaded)	8
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	248.000/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	4.20mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	5.40mm
Wire Size AWG	18
Wire/Cable Type	UL 2464
Electrical	
Current - Maximum per Contact	8.4A
Voltage - Maximum	300V AC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	2027040005-PK
Sales Drawing	2014400058-000

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per -ED/88/2018 (15 January 2019)	
Halogen-Free Status Not Low-Halogen	
For more information, please visit Contact US	
China ROHS ELV	Green Image Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
245135 Series

Mates With
Dual Row Plug Housing 5559
Dual Row Header 5566 , 5569 , 87427

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[245135-0820](#)