

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2068322201

Status:

Active

Overview:

Micro-Fit+ Connector System

Description:


Micro-Fit+ Vertical Header, 3.00mm Pitch, Dual Row, 22 Circuits, Tin (Sn) Plating, UL 94V-0, Glow-Wire Capable, Black

Documents:	
3D Model	Packaging Specification 2068320000-PK-000 (PDF)
3D Model (PDF)	Test Summary 2064600000-TS-000 (PDF)
Drawing (PDF)	Datasheet (PDF)
Product Specification 2064600000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	206832
Application	Power, Wire-to-Board
Overview	Micro-Fit+ Connector System
Product Name	Micro-Fit+
UPC	191130125302
Physical	
Breakaway	No
Circuits (Loaded)	22
Circuits (maximum)	22
Color - Resin	Black
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	High Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	2.686/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.18mm
Packaging Type	Tray
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	12.5A
Voltage - Maximum	600V AC (RMS)/DC

Material Info

Reference - Drawing Numbers



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

206832 Series

Mates With

Micro-Fit+ Receptacle 206461

Packaging Specification	2068320000-PK-000
Product Specification	2064600000-PS-000
Sales Drawing	2068320000-SD-000
Test Summary	2064600000-TS-000

This document was generated on 09/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[206832-2201](#)