




REF -50 OPTION SCREW
(WHERE APPLICABLE)




NOTES:

1. MATERIAL: SEE TABLE
2. INCH DIMENSIONS ARE SHOWN IN BRACKETS [XXX].
3. "XX" REFERS TO THE QUANTITY OF CIRCUITS.
4. ALL COMPONENTS ARE ROHS COMPLIANT.



4 CIRCUIT SHOWN



6	XX	SCREW&WASHER, 6-32X.250, PAN, PH/SL (-50 OPTION)	STEEL	ZN, CLEAR CHROMATE
5	XX	SCREW, 6-32X.250, BHD, PHIL-SLOT (-49 OPTION)	BRASS	NICKEL
4	XX	SCREW, 6-32X.250, BHD, PHIL-SLOT (STANDARD)	STEEL	ZN, CLEAR CHROMATE
3	XX	TERMINAL, SOLDER TURRET	BRASS	TIN
2	XX	MOUNTING PLATE	BRASS	NICKEL
1	1	INSULATOR, SR, W/MTG	THERMOPLASTIC	BLACK


ITEM	QTY	DESCRIPTION	MATERIAL	FINISH
------	-----	-------------	----------	--------

INITIAL RELEASE	EC NO: ETC2007-0073	2006/09/28	2006/09/28
DRW: JHLE	CHKD: JMACNEIL	APPR: JMACNEIL	2006/09/29
DESCRIPTION	REV	DATE	DATE
	A		

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)
▽=0	4 PLACES ± --- ± ---
▽=0	3 PLACES ± --- ± .005
	2 PLACES ± 0.13 ± .01
	1 PLACE ± 0.25 ± ---
	ANGULAR ± 2 °
	DRAFT WHERE APPLICABLE
	MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
MM/IN	2:1	INCH	
DRAWN BY	DATE	TITLE	
EHILE	2006/09/13	9.53MM [1.375] SR BTS	
CHECKED BY	DATE	ASSY, INSULATED TURRET	
JMACNEIL	2006/09/13	TERMINAL W/MTG	
APPROVED BY	DATE	MOLEX INCORPORATED	
JMACNEIL	2006/09/13		
MATERIAL NO.	DOCUMENT NO.	SHEET NO.	
SEE CHART	SD-38720-010	1 OF 2	

SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
B	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[38720-3210](#)