

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2138652233

Status:


Active

Overview:

Temperature Sensor Cable Assemblies

Description:

NTC Ring Temperature Sensor-to-Micro-Lock Plus Cable Assembly, 75.00mm Length, 3982 Beta Value, 2.25k# Resistance at 25°C with 2% Tolerance, Black



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	213865
Application	Temperature Sensing
Assembly Configuration	Dual Ended Connectors
Beta Value (K)	3985
Connector to Connector	Ring Term-to-Micro-Lock Plus
Overmolded	No
Overview	Temperature Sensor Cable Assemblies
Product Name	NTC Temperature Sensor
Resistance Tolerance (%)	2
Resistance at 25°C (kohms)	2.25
Stud Size	6 (M3.5)
Type	Discrete Wire Assembly
UPC	193264438488

Physical	
Cable Length	75.00mm
Circuits (Loaded)	2
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Nickel
Material - Plating Termination	Nickel, Tin
Material - Resin	PBT
Net Weight	1.732/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	1.25mm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.95mm
Wire Size AWG	26
Wire/Cable Type	PTFE, UL 10344

Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers	
Sales Drawing	2138601633-000, 2138652233-000

EU ELV

Not Relevant

EU RoHS

Compliant with
Exemption 15(a)

REACH SVHC

Contained Per -
D(2020)4578-DC (25
June 2020)
lead

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

213865 Series

Mates With

Micro-Lock Plus Vertical Header [505568](#)

 Micro-Lock Plus Right Angle Header
[505567](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[213865-2233](#)