

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202530346

Status:

Active

Overview:

Contrinex Inductive and Photoelectric

Description:

Contrinex Inductive Sensor, 6.5mm Diameter Smooth Housing, 2mm Operating Distance, Embeddable, NPN, NO, 3-pin M8 Connector, 45mm Housing Length



Documents:

Product Specification 1202530346-000 (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

|                               |                                       |
|-------------------------------|---------------------------------------|
| General                       |                                       |
| Product Family                | Sensors                               |
| Series                        | 120253                                |
| IP Rating                     | IP67                                  |
| Overview                      | Contrinex Inductive and Photoelectric |
| Product Category              | Inductive Sensors                     |
| Product Name                  | Contrinex                             |
| Type                          | Inductive                             |
| UPC                           | 191130065516                          |
| Physical                      |                                       |
| Connection                    | Connector (M8, 3-pin)                 |
| Length                        | 45mm                                  |
| Material - Housing            | Stainless Steel                       |
| Material - Sensing Face       | PA12                                  |
| Mounting Style                | Embeddable                            |
| Operating Distance            | 2mm                                   |
| Output                        | NO                                    |
| Sensor Housing Size           | 6.5mm dia. (smooth)                   |
| Temperature Range - Operating | -25° to +70°C                         |
| Electrical                    |                                       |
| Polarity                      | NPN                                   |
| Switching Frequency           | ≤ 5000 Hz                             |
| Material Info                 |                                       |
| Engineering Number            | DW-AS-621-065-001                     |
| Reference - Drawing Numbers   |                                       |
| Product Specification         | 1202530346-000                        |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Reviewed                                                  |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Reviewed                                                  |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

120253 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120253-0346