

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [2011964110](#)  
**Status:** **Active**  
**Overview:** Spot-On Wire-to-Board Connector System  
**Description:** Spot-On Terminal Position Assurance (TPA) Wire-to-Board Retainer, 2.00mm Pitch, 11 Circuits, Gray

**Documents:**

|                                                               |                                                                |
|---------------------------------------------------------------|----------------------------------------------------------------|
| <a href="#">3D Model</a>                                      | <a href="#">Application Specification 2011960000-A00 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                 | <a href="#">Application Specification 2011960000-A01 (PDF)</a> |
| <a href="#">3D Model (PDF)</a>                                | <a href="#">Packaging Specification 2011969200-201 (PDF)</a>   |
| <a href="#">Product Specification 2011960000-PS-000 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>           |
| <a href="#">Product Specification 2012000000-PS-000 (PDF)</a> |                                                                |

**General**

|                |                                                        |
|----------------|--------------------------------------------------------|
| Product Family | Accessories                                            |
| Series         | <a href="#">201196</a>                                 |
| Component Type | Terminal Position Assurance                            |
| Overview       | <a href="#">Spot-On Wire-to-Board Connector System</a> |
| Product Name   | Spot-On                                                |
| UPC            | 191128252843                                           |

**Physical**

|                               |                |
|-------------------------------|----------------|
| Circuits (Loaded)             | 11             |
| Circuits (maximum)            | 11             |
| Color - Resin                 | Gray           |
| Material - Resin              | Polyester      |
| Net Weight                    | 225.000/mg     |
| Number of Rows                | 1              |
| Packaging Type                | Bag            |
| Temperature Range - Operating | -40° to +105°C |

**Material Info**

**Reference - Drawing Numbers**

|                           |                                      |
|---------------------------|--------------------------------------|
| Application Specification | 2011960000-A00, 2011960000-A01       |
| Packaging Specification   | 2011969200-201                       |
| Product Specification     | 2011960000-PS-000, 2012000000-PS-000 |
| Sales Drawing             | 2011964150-000                       |



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[201196](#) Series

**Use With**

Spot-On Receptacle Housing [201196](#) ,  
[201200](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[201196-4110](#)