

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2130287000

Status:

Active

Overview:

CLIK-Mate Wire-to-Board Connectors

Description:

CLIK-Mate 1.50mm Pitch Wire-to-Board Male Crimp Terminal, 0.76µm Gold Plating, 24-26 AWG, Reel



Series image - Reference only

Documents:

Drawing (PDF)

Product Specification 5025780004-PS-000 (PDF)

Product Specification 5025781004-PS-000 (PDF)

Product Specification 5031490002-PS-000 (PDF)

Product Specification 5031491002-PS-000 (PDF)

Packaging Specification 2130289200-SPK-200 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	213028
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	CLIK-Mate Wire-to-Board Connectors
Product Name	CLIK-Mate
UPC	193264238606
Physical	
Durability (mating cycles max)	30
Gender	Male
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	22.967/mg
Packaging Type	Reel
Plating min - Mating	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.00-1.28mm
Wire Size AWG	24, 26
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	100V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	2130289200-SPK-200
Product Specification	5025780004-PS-000, 5025781004-PS-000, 5031490002-PS-000, 5031491002-PS-000
Sales Drawing	2130280000-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

213028 Series

Use With

CLIK-Mate Housing [503149](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool for 1.50mm Pitch CLIK-Mate Wire-to-Board Crimp Terminals, 24-28 AWG	2002187400
Extractor Tool for 1.50mm Pitch Wire-to-Board Crimp Terminal	638133700
FineAdjust Applicator for 1.50mm Pitch	639025000

Wire-to-Board Crimp
Terminals

Japan

Description	Product #
S-1 Applicator for CLIK-Mate Plug Terminals, 24-28 AWG	<u>5780473700</u>

This document was generated on 12/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[213028-7000](#) [213028-7000 \(Mouser Reel\)](#) [213028-7000 \(Cut Strip\)](#) [213028-7000 \(Loose Piece\)](#)