

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2002187000

Status:

Active

Overview:

Application Tooling

Description:

Hand Crimp Tool for SL Crimp Terminals, 24-30 AWG

Documents:

RoHS Certificate of Compliance (PDF)

| General | |
|--------------------------------|---|
| Product Family | Application Tooling |
| Series | 207129 |
| Comments | See Tooling Specification (PDF) Above |
| Function | Crimp |
| Geographic Area | Global |
| Level of Automation | Manual |
| More Detailed Tech Information | applicationtooling@molex.com |
| Overview | Application Tooling |
| Product Name | SL |
| Tool Type | Hand Crimp Tool |
| UPC | 195842130685 |
| Warranty Disclaimer | CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified. |

Material Info

| Reference - Drawing Numbers | |
|-------------------------------|----------------|
| Application Tooling Documents | 2002187000-000 |



Series image - Reference only

| | |
|---|--------------|
| EU ELV | |
| Not Reviewed | |
| EU RoHS | China RoHS |
| Not Reviewed | |
| REACH SVHC | |
| Not Reviewed | |
| Halogen-Free | |
| Status | |
| Not Reviewed | |
| For more information, please visit Contact US | |
| China ROHS | Not Reviewed |
| ELV | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

Search Parts in this Series

207129 Series

| Application Tooling Description | FAQ Product # |
|--|---------------|
| SL Crimp Terminal, Series 70058, Female, 24-30 AWG, with Tin (Sn) Plated Contact, Reel | 16020069 |
| SL Crimp Terminal, Series 70021, Male, with 0.38µm Selective Gold (Au) Plated Contact, 24-30 AWG, Reel | 16020077 |
| SL Crimp Terminal, Series 70021, Male, with 0.76µm Selective Gold (Au) Plated Contact, 24-30 AWG, Reel | 16020078 |
| SL Crimp Terminal, Series 70058, Female, 24-30 AWG, with 0.38µm | 16020082 |

Selective Gold (Au)
Plated Contact, Reel
SL Crimp Terminal, [16020083](#)
Series 70058,
Female, 24-30
AWG, with 0.76µm
Selective Gold (Au)
Plated Contact, Reel
SL Crimp Terminal, [16020096](#)
Series 70058,
Female, 24-30 AWG,
with Tin (Sn) Plated
Contact, Bag
SL Crimp Terminal, [16020097](#)
Series 70058,
Female, 24-30
AWG, with 0.38µm
Selective Gold (Au)
Plated Contact, Bag
SL Crimp Terminal, [16020098](#)
Series 70058,
Female, 24-30
AWG, with 0.76µm
Selective Gold (Au)
Plated Contact, Bag
SL Crimp Terminal, [16020105](#)
Series 70021, Male,
with Tin (Sn) Plated
Contact, 24-30 AWG,
Reel
SL Crimp Terminal, [16020108](#)
Series 70021, Male,
with Tin (Sn) Plated
Contact, 24-30 AWG,
Bag
SL Crimp Terminal, [16020109](#)
Series 70021,
Male, with 0.38µm
Selective Gold (Au)
Plated Contact,
24-30 AWG, Bag
SL Crimp Terminal, [16020110](#)
Series 70021,
Male, with 0.76µm
Selective Gold (Au)
Plated Contact,
24-30 AWG, Bag
SL Crimp Terminal, [16020117](#)
Series 70021,
Male, with 0.76µm
Selective Gold (Au)
Plated Contact,
22-24 AWG, Bag
SL Crimp Terminal, [16020119](#)
Series 71851,
Female, with 0.38µm
Selective Gold (Au)
Plated Contact,
24-30 AWG, Reel
SL Crimp Terminal, [16021109](#)
Series 71851,
Female, with 0.38µm
Selective Gold (Au)
Plated Contact,
24-30 AWG, Bag

SL Crimp Terminal, [16021112](#)
Series 71851,
Female, with Tin
(Sn) Plated Contact,
24-30 AWG, Reel
SL Crimp Terminal, [16021113](#)
Series 71851,
Female, with 0.76µm
Selective Gold (Au)
Plated Contact,
24-30 AWG, Reel
SL Crimp Terminal, [16021116](#)
Series 71851,
Female, with Tin
(Sn) Plated Contact,
24-30 AWG, Bag
SL Crimp Terminal, [16021117](#)
Series 71851,
Female, with 0.76µm
Selective Gold (Au)
Plated Contact,
24-30 AWG, Bag
SL Crimp Terminal, [700580097](#)
Female, 24-30
AWG, with 0.38µm
Selective Gold (Au)
Plated Contact, Bag

This document was generated on 10/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

200218-7000