

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5050704042

Status:

Active

Overview:

SlimStack Board-to-Board/Board-to-FPC Connectors

Description:

SlimStack Board-to-Board Plug, 0.35mm Pitch, SSB RP Series, 0.60 or 0.70mm Mated Height, 2.00mm Mated Width, 40 Circuits, Armor Nail, 0.25mm Fitting Nail Width

- Documents:
- 3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification 5050660000-015 (PDF)

Product Specification 5052700004-PS-000 (PDF)

Application Specification 5050660000-A06 (PDF)

Packaging Specification 5050709200-203 (PDF)

Datasheet (PDF)

Product Guide (PDF)

RoHS Certificate of Compliance (PDF)

Reference Guide (PDF)

General	
Product Family	PCB Headers
Series	505070
Application	Board-to-Board
Overview	SlimStack Board-to-Board/Board-to-FPC Connectors
Product Name	SlimStack
Series Name	0.35, SSB RP
UPC	191128261791
Physical	
Breakaway	No
Circuits (Loaded)	40
Circuits (maximum)	40
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Capable	No
Mated Height	0.60mm, 0.70mm
Mated Width	2.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	9.958/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.35mm
Pitch - Termination Interface	0.35mm
Plating min - Mating	0.100µm
Plating min - Termination	0.050µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	0.3A, 3.0A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series
505070 Series

Mates With
SlimStack SSB RP Receptacle 505066 , 505270

Application Specification	5050660000-A06
Packaging Specification	5050709200-203
Product Specification	5050660000-015, 5052700004-PS-000
Sales Drawing	5050700000-008, 5050701000-020

This document was generated on 09/22/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

505070-4042