

## Datasheet for 76650-0041

### General Information

<b>Part Number:</b>	76650-0041
<b>Manufacturer:</b>	Molex / Waldom
<b>Title:</b>	Solderless Terminal Kit
<b>Description:</b>	.250" Tab Size PVC Insulated Quick Disconnect Solderless Terminals
<b>Product Family:</b>	Quick Disconnect
<b>Certificates:</b>	(Molex Parts within this kit) - EU RoHS Compliant, UL and CSA
<b>Country of Origin:</b>	Kit assembled in U.S.A.

### Specifications

<b>Design Configuration:</b>	Wire-to-Wire / Solderless Terminals
<b>Size(s):</b>	.250"
<b>Insulation:</b>	PVC
<b>Current Rating:</b>	Per Proper Wire Specification
<b>Voltage:</b>	600 Volts
<b>Wire size:</b>	(22-18), (16-14) and (12-10)

### Product Highlights

Quick disconnects allow for quickly connecting or disconnecting a terminal. The front end of the terminal has a female-type receptacle which allows the terminal to slide onto and off of a male blade.

#### Features and Benefits

- Color-coded insulator allows easy identification of terminal size and wire gauge.
- A wire stop stamped into the crimp barrel prevents insertion of over-stripped wires.
- Terminal's funnel entrance is designed for increased crimping rates by speeding wire delivery into the crimp section and eliminating wire strand fold back.

#### Applications

- MRO (Maintenance Repair and Operations)
- Consumer applications
- Power applications
- Motor applications

## Datasheet for 76650-0041

### Bill of Materials for Part No. 76650-0041

Molex Part No.	Country of Origin	Description	Quantity in Kit
19023-0005	USA	Insulated .250" Male Quick Disconnects, 22-18 AWG	25
19023-0008	USA	Insulated .250" Male Quick Disconnects, 12-10 AWG	25
19023-0012	USA	Insulated .250" Male Quick Disconnects, 16-14 AWG	25
19017-0014	USA	Insulated .250" Female Quick Disconnects, 22-18 AWG	25
19017-0037	USA	Insulated .250" Female Quick Disconnects, 16-14 AWG	25
19017-0047	USA	Insulated .250" Female Quick Disconnects, 12-10 AWG	25

### Recommended Molex Tool(s) for Part No. 76650-0041\*

Molex Part No.	Country of Origin	Description
64001-0100 *	USA	Hand Crimp Tool (RHT-1990)
64001-0200 *	USA	Hand Crimp Tool (RHT-1991)
64001-1400 *	USA	Hand Crimp Tool (RHT-2100)
64001-1700 *	USA	Hand Crimp Tool (RHT-5757)
64001-2000 *	USA	Hand Crimp Tool (RHT-5758)
64001-4800 *	USA	Hand Crimp Tool (RHT-2251)

\*Tool(s) not included in kit. Tool(s) ordered separately.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

76650-0041