

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** 0423753269  
**Status:** Active  
**Description:** KK 100 Hdr Assy Bkwy 17 Ckt

**Documents:**

|                                                          |                                                                 |
|----------------------------------------------------------|-----------------------------------------------------------------|
| <a href="#">Drawing (PDF)</a>                            | <a href="#">Packaging Specification PK-40873-0041-001 (PDF)</a> |
| <a href="#">Product Specification PS-10-07-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>            |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**Application tooling part link**

|                               |            |
|-------------------------------|------------|
| Application Tooling Part Link | 11-20-1230 |
|-------------------------------|------------|

**General**

|                |              |
|----------------|--------------|
| Product Family | PCB Headers  |
| Series         | 42375        |
| Product Name   | KK 254       |
| UPC            | 800756722573 |

**Physical**

|              |         |
|--------------|---------|
| Flammability | 94V-0   |
| Net Weight   | 1.634/g |

**Electrical**

|                   |      |
|-------------------|------|
| Voltage - Maximum | 500V |
|-------------------|------|


**Solder Process Data**

|                                                |      |
|------------------------------------------------|------|
| Duration at Max. Process Temperature (seconds) | 005  |
| Lead-freeProcess Capability                    | WAVE |
| Max. Cycles at Max. Process Temperature        | 001  |
| Process Temperature max. C                     | 235  |

**Material Info**

**Reference - Drawing Numbers**

|                         |                   |
|-------------------------|-------------------|
| Packaging Specification | PK-40873-0041-001 |
| Product Specification   | PS-10-07-001      |
| Sales Drawing           | SD-42375-001-001  |



Series image - Reference only

**EU ELV**

Not Relevant

**EU RoHS**

Compliant

**China RoHS**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

Not Low-Halogen

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**

42375 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

42375-3269