

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190270071](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	207126
Comments	The Crimp Tape Module 640162000 is a base unit that will work like an applicator in a Molex TM-3000 638017200 , 638017300 industry standard crimp press or the Molex TM-4000 638017600 industry standard crimp press. The Crimp Tape Module will accept all ATP-301 and ATP-201 style crimp dies. This Crimp Tape Module will allow customers to process most of Molex's Mylar Tape product from 2 AWG uninsulated and 4 AWG insulated products and up. The Crimp Tape Module will NOT work in any other industry standard crimp press or wire process machine. These ATP-301 style die sets can be used in the older style suitcase presses.
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Crimp Module
UPC	800753041066
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info
Engineering Number ATP-BB-175

Reference - Drawing Numbers
Application Tooling Documents
ATS-190270071-001, ATS-TOOLING-ID-ATP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001,



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207126](#) Series

Use With
Molex Crimp Tape Module [640162000](#) used with Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex ATP-301 Press: [192280030](#) and Molex ATP-101 style presses.

Application Tooling Description	FAQ Product #
Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Mylar Tape, Tab 2.79 x 0.51mm	190160036
Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Mylar Tape, Tab 2.79 x 0.81mm	190160038
Krimptite Quick Disconnect, Female, for 14-16	190160041

TM-640160065TH-001, TM-640160065TW-001,
TM-640160065VN-001

(2.00-1.30mm²) Wire,
Mylar Tape, Tab 4.75
x 0.81mm
Krimptite Quick 190160042
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Mylar Tape, Tab 4.75
x 0.51mm
Krimptite Quick 190160043
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Mylar Tape, Tab 6.35
x 0.81mm
Krimptite Quick 190220009
Disconnect,
Male, for 18-22
(0.80-0.35mm²) Wire,
Mylar Tape, Tab 4.75
x 0.51mm
Krimptite Star Ring 190740002
Tongue Terminal for
18-22 AWG Wire,
Stud Size 6 (M3.5),
Mylar Tape Carrier
Krimptite Star Ring 190740006
Tongue Terminal for
18-22 AWG Wire,
Stud Size 8 (M4),
Mylar Tape Carrier
Krimptite Star Ring 190740008
Tongue Terminal for
18-22 AWG Wire,
Stud Size 10 (M5),
Mylar Tape Carrier
Krimptite Steel 190740010
Star Ring Tongue
Terminal for 18-22
AWG Wire, Stud
Size 6 (M3.5), Mylar
Tape Carrier
Krimptite Steel 190740012
Star Ring Tongue
Terminal for 18-22
AWG Wire, Stud
Size 8 (M4), Mylar
Tape Carrier
Krimptite Steel 190740014
Star Ring Tongue
Terminal for 18-22
AWG Wire, Stud
Size 10 (M5), Mylar
Tape Carrier

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19027-0071