

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: [0622018780](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Daughter Card Module Installation Press-In Tool

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	207123
Function	Insertion
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	884982281318
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-622018780



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per -ED/01/2018 (15 January 2018) Halogen-Free Status Not Relevant For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
	Not Relevant Not Relevant Not Contained

Search Parts in this Series
[207123](#) Series

Use With
Impact Daughtercard Assembly (3-Pair by 6 Column Assemblies) [76170](#) Series

Application Tooling Description	FAQ Product #
Impact 100 Ohm 3 Pair Right-Angle Daughtercard Receptacle, Unguided, 6 Columns, 54 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free	761701006
Impact 100 Ohm 3 Pair Right-Angle Daughtercard Receptacle, Unguided, 6 Columns, 54 Circuits, Plated Through Hole	761701036

Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761703006
3 Pair Right-Angle
Daughtercard
Receptacle, Left
Guided, 6 Columns,
54 Circuits, Plated
Through Hole
Dimension 0.46mm,
Lead Free
Impact 100 Ohm 761703036
3 Pair Right-Angle
Daughtercard
Receptacle, Left
Guided, 6 Columns,
54 Circuits, Plated
Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761705006
3 Pair Right-Angle
Daughtercard
Receptacle, Right
Guided, 6 Columns,
54 Circuits, Plated
Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761705036
3 Pair Right-Angle
Daughtercard
Receptacle, Right
Guided, 6 Columns,
54 Circuits, Plated
Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761705236
3 Pair Right-Angle
Daughtercard
Receptacle, Right
Guided, 6 Columns,
54 Circuits, Plated
Through Hole
Dimension 0.39mm,
Polarizing Key
Position A, Lead-
Free

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8780](#)