

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638136900

Status:


Active

Overview:

Application Tooling

Description:

Extractor Tool for 2.80mm Crimp Terminals



Series image - Reference only

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207121
Comments	See Tooling Specification (PDF) Above
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Extraction Hand Tool
UPC	884982141438
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-638136900-001

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207121 Series

Use With

Application Tooling Description	FAQ Product #
MOX Crimp Terminal, Female, 0.635mm, 20-24 AWG (0.22-0.60mm²), Reel, Tin (Sn)	986581211
MOX Crimp Terminal, Female, 0.635mm, 18-22 AWG (0.75mm²), Reel, Tin (Sn)	986581212
MOX Crimp Terminal, Female, 0.635mm, 20-24 AWG (0.22-0.50mm²), Reel, Tin (Sn)	986581213
MOX Crimp Terminal, Female, 0.635mm,	986581221

	20-24 AWG (0.22-0.60mm²), Reel, Selective Gold MOX Crimp	<u>986581222</u>
	Terminal, Female, 0.635mm, 18-22 AWG (0.75mm²), Reel, Selective Gold MOX Crimp	<u>986581223</u>
	Terminal, Female, 0.635mm, 20-24 AWG (0.22-0.50mm²), Reel, Selective Gold MOX Crimp	<u>986581231</u>
	Terminal, Female, 0.635mm, 20-24 AWG (0.22-0.60mm²), Reel, 2 Points Selective Gold MOX Crimp	<u>986581232</u>
	Terminal, Female, 0.635mm, 18-22 AWG (0.75mm²), Reel, 2 Points Selective Gold MOX Crimp	<u>986581233</u>
	Terminal, Female, 0.635mm, 20-24 AWG (0.22-0.50mm²), Reel, 2 Points Selective Gold	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63813-6900](#)