

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0732511351

Status:

Active

Overview:

SMA RF Connectors

Description:

50 Ohms, SMA Jack, Vertical, PCB SMT, Gold (Au) Body, Tape and Reel (400 Pieces)

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-89675-346-001 (PDF)

Packaging Specification SD-73251-135-PKG-001 (PDF)

RoHS Certificate of Compliance (PDF)

|                       |                       |
|-----------------------|-----------------------|
| General               |                       |
| Product Family        | RF/Coax Connectors    |
| Series                | 73251                 |
| Overview              | SMA RF Connectors     |
| Product Name          | SMA                   |
| Style                 | PCB                   |
| Type                  | Subminiature          |
| UPC                   | 822350157377          |
| Wire/Cable Type       | N/A                   |
| Physical              |                       |
| Gender                | Jack                  |
| Keying to Mating Part | None                  |
| Net Weight            | 1.265/g               |
| Orientation           | Straight              |
| PCB Mounting          | Surface Mount         |
| Packaging Type        | Embossed Tape on Reel |
| Panel Mount           | No                    |
| Panel Mount Method    | N/A                   |
| Reverse Polar         | No                    |

|                 |                             |
|-----------------|-----------------------------|
| Electrical      |                             |
| Frequency       | 18 GHz                      |
| Impedance       | 50Ω                         |
| Power / Voltage | VOLTAGE: 500 Vrms@Sea Level |

|                                                |        |
|------------------------------------------------|--------|
| Solder Process Data                            |        |
| Duration at Max. Process Temperature (seconds) | 010    |
| Lead-freeProcess Capability                    | REFLOW |
| Max. Cycles at Max. Process Temperature        | 002    |
| Process Temperature max. C                     | 260    |

Material Info

|                             |                      |
|-----------------------------|----------------------|
| Reference - Drawing Numbers |                      |
| Packaging Specification     | SD-73251-135-PKG-001 |
| Product Specification       | PS-89675-346-001     |
| Sales Drawing               | SD-73251-135-001     |



Series image - Reference only

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant with Exemption 6(c)                                 |               |
| REACH SVHC                                                    |               |
| Contained Per - D(2021)4569-DC (8 July 2021)                  |               |
| Lead                                                          |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Low-Halogen                                                   |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | 50 Image      |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

73251 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

73251-1351