

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018695

Status:

Active

Overview:

Description:

Press-In Tool for Vertical Signal Module Assembly, 5-Pair by 10-Column

General

Product Family	Application Tooling
Series	207123
Function	Insertion
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	application_tooling
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	883906497163
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents	ATS-622018695-001, TM-622018799-001
-------------------------------	-------------------------------------

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207123 Series

Use With

76530 Impact Vertical Mezzanine Signal Module Assembly

Application Tooling

Description

FAQ

Product #

Impact 100 Ohm 765301020

5 Pair Mezzanine Receptacle, 28mm Stack Height, Unguided, 10 Columns, 150 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free

Impact 100 Ohm 765301030

5 Pair Mezzanine Receptacle, 38mm Stack Height, Unguided, 10 Columns, 150 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free

Impact 100 Ohm 765301040

5 Pair Mezzanine Receptacle, 40mm Stack Height, Unguided, 10 Columns, 150 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free

Impact 100 Ohm	<u>765303030</u>
5 Pair Mezzanine	
Receptacle, 38mm	
Stack Height, Left	
Guided, 10 Columns,	
150 Circuits, Plated	
Through Hole	
Dimension 0.39mm,	
Lead-Free	
Impact 100 Ohm	<u>765303040</u>
5 Pair Mezzanine	
Receptacle, 40mm	
Stack Height, Left	
Guided, 10 Columns,	
150 Circuits, Plated	
Through Hole	
Dimension 0.39mm,	
Lead-Free	
Impact 100 Ohm	<u>765305030</u>
5 Pair Mezzanine	
Receptacle, 38mm	
Stack Height, Right	
Guided, 10 Columns,	
150 Circuits, Plated	
Through Hole	
Dimension 0.39mm,	
Lead-Free	
Impact 100 Ohm	<u>765305040</u>
5 Pair Mezzanine	
Receptacle, 40mm	
Stack Height, Right	
Guided, 10 Columns,	
150 Circuits, Plated	
Through Hole	
Dimension 0.39mm,	
Lead-Free	

This document was generated on 06/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8695](#)