

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638853800

Status:

Active

Overview:

Application Tooling

Description:

Mini-Mac Applicator


Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207127
Comments	The Molex Tape Applicator requires an industry standard crimp press with a 4way air like the Molex TM-3000: 638017200 , 638017300 , and the Molex TM-4000: 638017600
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Mini-Mac
Tool Type	Applicator
UPC	800756748412
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-638853800-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: 638017200 , 638017300 , Molex TM-4000: 638017600 , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
Krimptite Ring Tongue Terminal for 18-22 AWG Wire	190690028
Krimptite Ring Tongue Terminal for 18-22 AWG Wire	190690030
Krimptite Ring Tongue Terminal for 18-22 AWG Wire	190690032
Krimptite Ring Tongue Terminal for 18-22 AWG Wire	190690034
Krimptite Ring Tongue Terminal for 18-22 AWG Wire	190690036

Krimptite Ring	<u>190690038</u>
Tongue Terminal for	
18-22 AWG Wire	
Krimptite Ring	<u>190690044</u>
Tongue Terminal for	
18-22 AWG Wire	
Krimptite Ring	<u>190690046</u>
Tongue Terminal for	
18-22 AWG Wire	
Krimptite Ring	<u>190690050</u>
Tongue Terminal for	
18-22 AWG Wire	
Krimptite Ring	<u>190690055</u>
Tongue Terminal for	
18-22 AWG Wire	
Krimptite Ring	<u>190690057</u>
Tongue Terminal for	
18-22 AWG Wire	
Krimptite Ring	<u>190690062</u>
Tongue Terminal for	
18-22 AWG Wire	
Krimptite Snap	<u>190980019</u>
Spade Tap for 18-22	
AWG Wire, Stud	
Size 5-6 (M3-3.5),	
Mylar Tape Carrier	
Krimptite Snap	<u>190980080</u>
Spade Tap for 18-22	
AWG Wire, Stud	
Size 8 (M4), Mylar	
Tape Carrier	
Krimptite Snap	<u>190980081</u>
Spade Tap for 18-22	
AWG Wire, Stud	
Size 10 (M5), Mylar	
Tape Carrier	
Krimptite Flanged	<u>191180022</u>
Spade Tongue	
Terminal for 18-22	
AWG Wire, Stud	
Size 6 (M3.5),	
Length 14.12mm,	
Mylar Tape Carrier	
Krimptite Flanged	<u>191180024</u>
Spade Tongue	
Terminal for 18-22	
AWG Wire, Stud	
Size 8 (M4), Mylar	
Tape Carrier	
VersaKrimp Ring	<u>191930008</u>
Tongue Terminal for	
18-22 AWG Wire	
VersaKrimp Ring	<u>191930011</u>
Tongue Terminal for	
18-22 AWG Wire	
VersaKrimp Ring	<u>191930013</u>
Tongue Terminal for	
18-22 AWG Wire	
VersaKrimp Ring	<u>191930015</u>
Tongue Terminal for	
18-22 AWG Wire	
VersaKrimp Ring	<u>191930017</u>
Tongue Terminal for	
18-22 AWG Wire	

VersaKrimp Ring	<u>191930022</u>
Tongue Terminal for	
18-22 AWG Wire	
VersaKrimp Ring	<u>191930024</u>
Tongue Terminal for	
18-22 AWG Wire	
VersaKrimp Ring	<u>191930035</u>
Tongue Terminal for	
18-22 AWG Wire	
VersaKrimp Ring	<u>191930037</u>
Tongue Terminal for	
18-22 AWG Wire	
VersaKrimp Ring	<u>191930042</u>
Tongue Terminal for	
18-22 AWG Wire	
Krimptite Wire Pin	<u>192110004</u>
Terminal for 22-18	
AWG Wire, Mylar	
Tape Carrier	
VersaKrimp Metric	<u>193230207</u>
Ring Terminal for	
M2.5 Stud Size	
(#4), Un-insulated,	
Adhesive Tape on	
Reel	
VersaKrimp Metric	<u>193230208</u>
Ring Terminal for M3	
Stud Size (#5), Un-	
insulated, Adhesive	
Tape on Reel	
VersaKrimp Metric	<u>193230209</u>
Ring Terminal	
for M3-3.5 Stud	
Size (#5-#6), Un-	
insulated, Adhesive	
Tape on Reel	
VersaKrimp Metric	<u>193230210</u>
Ring Terminal for M4	
Stud Size (#8), Un-	
insulated, Adhesive	
Tape on Reel	
VersaKrimp Metric	<u>193230211</u>
Ring Terminal for M5	
Stud Size (#10), Un-	
insulated, Adhesive	
Tape on Reel	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63885-3800