

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638913000

Status:

Active

Overview:

Application Tooling

Description:

Mini-Mac Applicator

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207127

See Tooling Specification (PDF) Above

Crimp

Global

Automatic, Semi-Automatic

applicationtooling@molex.com

Application Tooling

Mini-Mac

Applicator

800756656038

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

4802.284/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638913000-001, TM-638000100-001, TM-638000100SP-001

Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

Not Reviewed

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: 638017200 , 638017300 , Molex TM-4000: 638017600 , Molex TM-2000: 638008300 , 638008400 , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
Panel Grounding Clip Crimp Terminal 42172, 16-18 AWG, 301 Stainless Steel, 0.89mm Panel Thickness, 0.20mm Dimension F	40062003
Panel Grounding Clip Crimp Terminal 42172, 16-18 AWG, 301 Stainless Steel, 1.27mm Panel Thickness	40062005
Panel Grounding Clip Crimp Terminal 42172, 16-18 AWG, 301 Stainless Steel, 1.91mm Panel Thickness	40062013
Panel Grounding Clip Crimp Terminal 42172, 14 AWG, 301 Stainless Steel, 0.89mm Panel Thickness	40062014

Panel Grounding 40062024
Clip Crimp Terminal
42172, 16-18 AWG,
301 Stainless Steel,
0.89mm Panel
Thickness, 0.10mm
Dimension F

This document was generated on 01/25/2022
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63891-3000](#)