

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1121130009

Status:


Active

Overview:

PC Network Interface Cards

Description:

SST DN4 Card, DeviceNet MultiSlave, 1 Channel, PCI 3.3/ 5V, Full Bracket - DLL/LIB - Simulation



Documents:

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

|                               |                                                                                                                 |
|-------------------------------|-----------------------------------------------------------------------------------------------------------------|
| <b>General</b>                |                                                                                                                 |
| Product Family                | Network Interface                                                                                               |
| Series                        | 112113                                                                                                          |
| Application                   | IO Control                                                                                                      |
| Approvals                     | CE, ODVA certified                                                                                              |
| Comments                      | DeviceNet Multi-Adapter, full bracket, DeviceNet Multi-Adapter, full bracket                                    |
| Exclude SD Check              | Yes                                                                                                             |
| Overview                      | PC Network Interface Cards                                                                                      |
| Product Literature Order No   | 987650-5071                                                                                                     |
| Product Name                  | SST                                                                                                             |
| Protocol                      | DeviceNet                                                                                                       |
| Protocol Detail               | DeviceNet Adapter, DeviceNet Multi Adapter                                                                      |
| Software Downloads            | SST-DN4MS-PCU                                                                                                   |
| Type                          | DeviceNet Card                                                                                                  |
| UPC                           | 78172513605                                                                                                     |
| <b>Physical</b>               |                                                                                                                 |
| Channels                      | 1                                                                                                               |
| Communication Speed           | 1 Mbaud (CAN only), DeviceNet 125, 250, 500 Kbaud                                                               |
| Interface                     | DLL                                                                                                             |
| Mounting Style                | PC Slot                                                                                                         |
| Network Connection Type       | DeviceNet (5 pin)                                                                                               |
| Operating System              | Windows7, Windows8/8.1, Windows Server 2003, Windows Server 2008, Windows Server 2012, Windows Vista, WindowsXP |
| Packaging Type                | Carton                                                                                                          |
| Processor                     | 64 Mhz NIOS                                                                                                     |
| Slot                          | Universal PCI 3.3V/5V                                                                                           |
| Temperature Range - Operating | 0°C to +60°C                                                                                                    |
| <b>Electrical</b>             |                                                                                                                 |
| Current - Maximum Input       | 600.0 mA on PC Bus - 2-channel                                                                                  |
| EMC                           | N/A                                                                                                             |
| Supply Voltage                | 24V DC Network, 3.3/5V Bus                                                                                      |
| <b>Material Info</b>          |                                                                                                                 |
| Engineering Number            | SST-DN4MS-PCU                                                                                                   |

|                                                               |                   |
|---------------------------------------------------------------|-------------------|
| <b>EU ELV</b>                                                 |                   |
| Not Reviewed                                                  |                   |
| <b>EU RoHS</b>                                                | <b>China RoHS</b> |
| Not Reviewed                                                  |                   |
| <b>REACH SVHC</b>                                             |                   |
| Not Reviewed                                                  |                   |
| <b>Halogen-Free</b>                                           |                   |
| <b>Status</b>                                                 |                   |
| Not Reviewed                                                  |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Not Reviewed      |
| ELV                                                           | Not Reviewed      |
| RoHS Phthalates                                               | Not Reviewed      |

Search Parts in this Series

112113 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[112113-0009](#)