

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300620032

Status:


Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change Double-Ended Cordset, 3 Poles, Male (Straight) to Female (Straight), 16 AWG, PVC Cable, 2.0m (6.56') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E258922
General	
Product Family	Industrial Cordsets
Series	130062
Connector End A	Mini-Change
Connector End B	Mini-Change
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Mini-Change Connectors
Product Name	Mini-Change
Protocol	N/A
Region	Europe
Type	Double Ended
UPC	78678859105
Physical	
Cable Diameter	N/A
Cable Length	2.0m (6.56')
Color - Cable Jacket	Gray
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold over Nickel
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	16
Wire/Cable Type	STOOW
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V
Material Info	
Engineering Number	113030A45M020
Reference - Drawing Numbers	
Sales Drawing	SD-130062-014

EU ELV

Not Relevant

EU RoHS

Compliant with
Exemption 6(c)

REACH SVHC

Contained Per -
ED/79/2015 (17
December 2015)
Arsenic acid
(H3AsO4), lead(2+)
salt (1:1)
Arsenic acid
(H3AsO4), triethyl
ester
Dibutylphthalate
(DBP)
Diarsenic-pentaoxide
Diarsenic-trioxide
5-tert-Butyl-2,4,6-
trinitro-m-xylene
Di-(2-
ethylhexyl)phthalate
(DEHP)
Butylbenzylphthalate
(BBP)
2,4-dinitrotoluene
1-Methyl-2-
pyrrolidone
sodium
peroxometaborate
Hydrazine
HBCDD
Sodium perborate;
perboric acid, sodium
salt

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS
ELV

China RoHS

50 Image
Not Relevant

RoHS Phthalates

Contained:
DBP,DEHP,BBP

Search Parts in this Series

[130062](#) Series

This document was generated on 05/02/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300620032