

CMP4010

Wi-Fi + BLE

Connectivity for IoT

Feature rich & high performance


Built for high performance and harsh environments, CEL's Hosted or Hostless IoT connectivity module is perfect for applications requiring multiple technologies for local+remote connectivity, a simple method for commissioning Wi-Fi, low power, processing at the edge, running a complete application, data/audio/video applications, and more. Below are some key highlights of this leading-edge solution.

WIRELESS FEATURES

- Single-Band 802.11 b/g/n
 - Tx: +18 dBm
 - Wi-Fi Direct & Soft AP
 - Wake on RF
- BLE 5.0 and BT Mesh
 - Tx: +4.5dBm
 - 2Mbit PHY
 - Co-existence Manager
- Low Power Consumption
- Long Range & Broad Coverage
- High Noise Immunity
- High Throughput

APPLICATION RESOURCES

- Dual-core 32-bit Arm Cortex-M33 & M23 compatible
- 8/2MB Flash, 4MB PSRAM, 512kB SRAM
- 35 GPIO, USB/UART/SPI/I2C
- RTC, I2S & Audio CODEC
- Cap Touch & Keyscan
- Advanced Security Features



SOFTWARE DEVELOPMENT TOOLS

- HOSTED: AT Command Set
- HOSTLESS: RTOS Support - FreeRTOS, Arm Mbed
- Toolchain Support: IAR, GCC
- AWS/Google Cloud/Azure Certified Platform
- Alexa/Smart Assistant and Homekit Support

REFERENCE CODE AVAILABLE

- Wi-Fi Provisioning via BLE
- USB UVC Camera Interface @1280x720 30fps (~3.5MB/s)
- OTA FW Updates
- Fast Connect
- Remote Connectivity

APPLICATIONS

- Connected Home...Lights, switches, outlets, circuit breakers, door cameras, wall displays, appliances, timers
- Safety...CO2, Smoke Detectors
- Residential HVAC...Thermostats, AC units, furnace, sensors
- Security...Locks, keypads, cameras
- C&I Lighting...control adaptors, sensors, switches
- Building Automation...HVAC controllers, VAVs, security devices, shade controls, lighting controls & sensors
- Smart Energy...generators, load switches, power modules

SAMPLING KITS AVAILABLE

[DigiKey - Evaluation Board - CMP4010-EVB](#)

[Mouser - Evaluation Board - CMP4010-EVB](#)

Questions? Call Us
(408) 919-2500

www.cel.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CEL:

[CMP4010-1-R](#) [CMP4010-1C-R](#) [CMP4010-1-B](#) [CMP4010-1C-B](#)