



## NE8FBH-C5-S

Horizontal PCB mount RJ45 receptacle, CAT5e, shielded, B-Series cutout with latch lock, max. panel thickness 3 mm

The etherCON Series is a ruggedized and lockable RJ45 connector system, optimized for pro audio, video and lightning network applications. The chassis connectors are shaped to fit into standardized panels out of the entertainment industry. NEUTRIK etherCON's are capable of PoE++ up to 100 W (cf. White Paper)

The B-Series offers a space saving design and a rugged metal front plate.

Attention! Does not intermate with CAT6 cable connector NE8MC6-MO and NKE6S\* cables.

## Features & Benefits

- ✓ Accommodates rugged etherCON NE8MC\* or any standard RJ45 plug
- ✓ Approved latch lock system
- ✓ Ground panel connection
- ✓ PoE type 4 class 8 (100W) acc. IEEE 802.3bt
- ✓ CAT5e according to ISO/IEC 11801 and TIA/EIA 568A/B

## Technical Information

Product	
Title	NE8FBH-C5-S
Gender	female

Electrical	
Contact resistance	< 50 mΩ
Dielectric strength	1 kVdc
Frequencyrange	1 - 100 MHz
Insulation resistance	> 0.5 GΩ
Rated current per contact	1.5 A
Rated voltage	≤ 57 V
Transmission performance	CAT5e acc. to TIA/EIA 568A/B component specifications CAT5e acc. to ISO/IEC 11801 component specifications
Power over Ethernet	PoE type 4 class 8 (90 W) acc. IEEE 802.3bt

<b>Mechanical</b>	
<b>Insertion force</b>	≤ 20 N
<b>Withdrawal force</b>	≤ 20 N
<b>Lifetime</b>	> 1000 mating cycles
<b>Panel thickness</b>	max. 3 mm (0.12")
<b>Wiresize</b>	
<b>Wiring</b>	Horizontal PCB mount
<b>Locking device</b>	Latch lock
<b>Mounting direction</b>	Rear mounting
<b>Chassis shape</b>	B
<b>Mounting</b>	A-Screw

<b>Material</b>	
<b>Contact plating</b>	0.2 µm Au over Ni plating
<b>Contacts</b>	Bronze (CuSn8)
<b>Locking element</b>	Ck 67 steel, treated
<b>Locking element plating</b>	Nickel
<b>Shell</b>	PBT D202G30

Environmental	
Flammability	UL 94 V-0
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C
Standard compliance	ISO/IEC 11801-1 Ed. 1.0 (2017-11) IEC 60603-7-3 Ed.2.0 (2010-04) IEC 60512-99-002 Ed.2.0 (2022-01) IEC 60512-9-3 (2011-06)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NE8FBH-C5-S](#)