

4G/ LTE Magnetic Mount Antenna



AEACAD097015-S698

97 x Ø 15 mm

RoHS/RoHS II Compliant

MSL - 1

FEATURES

- Operates in 700-2700 MHz
- Linear polarization
- High gain of 5 dBi
- Omni-directional pattern
- VSWR 2.5

APPLICATIONS

- 4G/LTE radios
- Gateways
- Set-Top boxes
- Security
- IoT
- M2M
- Transportation
- Smart agriculture

Electrical Characteristics

Parameters	Min.	Typ.	Max	Units	Note
Frequency Range		700 ~ 2700		MHz	
VSWR			2.5		
Polarization Model	Linear				
Impedance		50		Ω	
Gain		5.0		dBi	Zenith

Mechanical Characteristics

Parameters	Note
Connector	SMA
Cable Type	RG58
Cable Length	3M
Mounting	Magnetic
Dimensions	97 x Φ 62 mm



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08.15.2018

ABRACON IS
ISO9001-2015
CERTIFIED

4G/ LTE Magnetic Mount Antenna




AEACAD097015-S698

97 x Ø 15 mm

RoHS/RoHS II Compliant

MSL - 1

Dimensions



Product Image



4G/ LTE Magnetic Mount Antenna




AEACAD097015-S698

97 x Ø 15 mm

RoHS/RoHS II Compliant

MSL - 1

VSWR



Gain and Efficiency

Frequency(MHz)	Efficiency (%)	Gain (dBi)
700	0.65	4.87
824	0.62	3.08
868	0.61	3.09
960	0.60	2.56
1710	0.53	2.85
1850	0.59	2.92
1990	0.52	1.81
2170	0.57	2.46
2690	0.58	2.66



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08.15.2018

ABRACON IS
ISO9001-2015
CERTIFIED

4G/ LTE Magnetic Mount Antenna






AEACAD097015-S698

97 x Ø 15 mm

RoHS/RoHS II Compliant

MSL - 1

Radiation Pattern



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08.15.2018

ABRACON IS
ISO9001-2015
CERTIFIED



AEACAD097015-S698


97 x Ø 15 mm

RoHS/RoHS II Compliant


MSL - 1

Radiation Pattern


3D Radiation Patterns




698 MHz




824 MHz




868 MHz




960 MHz




1710 MHz




1850 MHz



1900 MHz



2170 MHz



2690 MHz

4G/ LTE Magnetic Mount Antenna



AEACAD097015-S698

97 x Ø 15 mm

RoHS/RoHS II Compliant

MSL - 1

Packaging

Each 35 x 35 x 30cm size carton includes 50 pcs antenna, weighs 15 kg



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08.15.2018

ABRACON IS
ISO9001-2015
CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[AEACAD097015-S698](#)