


Multilayer Ferrite Chip Inductor (High Current)



AIML-0603HC Series

Request Samples



Check Inventory



1.6 x 0.8 x 0.8mm
RoHS/RoHS II Compliant
MSL Level = 1

Features

- Monolithic structure for higher reliability, compact size, & lightweight
- Magnetically shielded design to eliminate cross coupling
- Excellent solderability and heat resistance for reflow soldering
- Perfect shape for PCB mounting with no polarity

Applications

- DC/DC converter circuit for Front End Module such as Skyworks Solution.
- Portable AV equipment such as Digital Camera, Camcorder remote Control.

Electrical Specifications

Part No.	L(μ H)	Tolerance	Test Freq.	SRF	DCR	Isat	Irms
		(%)	(MHz)	(MHz)	(Ω)	(mA)	(mA)
AIML-0603HC-R22M	0.22	M	1	200	0.10	1350	1250
AIML-0603HC-R33M	0.33	M	1	190	0.13	1250	1200
AIML-0603HC-R47M	0.47	M	1	180	0.15	1000	1100
AIML-0603HC-R68M	0.68	M	1	160	0.18	950	1150
AIML-0603HC-1R0M	1.0	M	1	125	0.20	650	1000
AIML-0603HC-1R5M	1.5	M	1	100	0.23	420	900
AIML-0603HC-1R8M	1.8	M	1	100	0.26	300	800
AIML-0603HC-2R2M	2.2	M	1	80	0.30	250	850
AIML-0603HC-2R7M	2.7	M	1	90	0.34	180	750
AIML-0603HC-3R3M	3.3	M	1	100	0.40	125	700
AIML-0603HC-4R7M	4.7	M	1	65	0.40	65	700
AIML-0603HC-6R8M	6.8	M	1	45	0.56	130	500
AIML-0603HC-100M	10	M	1	35	0.36	60	500

Operating Temperature Range: -55°C to + 125°C

Storage Temperature Range: -55°C to + 125°C

Test Conditions and equipment

L, Q: HP4291 Impedance Analyzer DCR: HP4263A LCR meter

SRF: HP4291 Impedance analyzer

Irms: HP4291 Impedance Analyzer, DC power HP6632 and Adapter HP16200. Current when temperature of the product reaches +40°C.

Isat: HP4291 Impedance Analyzer, DC power HP6632 and Adapter HP16200. $\Delta L/L$ (initial) $\geq$ -30%



5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION A: 9/20/2016

ABRACON IS
ISO9001-2015
CERTIFIED

Multilayer Ferrite Chip Inductor (High Current)



AIML-0603HC Series

Request Samples




Check Inventory



1.6 x 0.8 x 0.8mm
RoHS/RoHS II Compliant
MSL Level = 1

Mechanical Specifications



L	W	T	a1, a2
1.60±0.15	0.80±0.15	0.80±0.15	0.30±0.20

Part Identification


AIML-0603HC- - -

Inductance Code
Please refer to the table above

Tolerance
M: ±20%


Packaging
T: Tape and Reel
(4kpcs / reel)

Materials



	Part Name	Material
1	Base Material	Ferrite (Ni-Cu-Zn series)
2	Internal Conductor	Ag
3	Terminal Electrode	Ag
4	Electrode Plating	Ni-Sn

Multilayer Ferrite Chip Inductor (High Current)



AIML-0603HC Series

Request Samples




Check Inventory



1.6 x 0.8 x 0.8mm
RoHS/RoHS II Compliant
MSL Level = 1

Reflow Profile



Zone	Description	Temperature	Times
1	Preheat	$T_{SMIN} \sim T_{SMAX}$ $150^\circ\text{C} \sim 200^\circ\text{C}$	60 ~ 180 sec.
2	Reflow	T_L 217°C	60 ~ 150 sec.
3	Peak heat	T_P $260^\circ\text{C} \pm 5^\circ\text{C}$	3~4 sec. MAX

Multilayer Ferrite Chip Inductor (High Current)



AIML-0603HC Series

Request Samples




Check Inventory




1.6 x 0.8 x 0.8mm
RoHS/RoHS II Compliant
MSL Level = 1

Packaging

T: 4,000pcs/Reel



A	B	C	D	E	F	G	H	ΦJ	t(max)
1.05±0.15	1.9±0.15	8.0±0.3	3.5±0.05	1.75±0.1	4.0±0.1	2.0±0.05	4.0±0.1	1.5+0.1/-0	1.0±0.05



A	178±2
B	60±2
C	13.0±0.5
D	21.0±0.8
E	2.0±0.5
W	10.0±1.15
t	1.2±0.2
R	1.0±0.25

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln, Spicewood TX 78669
 Phone: 512-371-6159 Fax: 512-351-8858
 For terms and conditions of sales, please visit:
www.abracon.com

REVISION A: 9/20/2016

ABRACON IS
 ISO9001-2015
 CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[AIML-0603HC-3R3M-T](#) [AIML-0603HC-4R7M-T](#)