

SMD ONE PORT 433.92 MHz SAW RESONATOR



5 x 5 x 1.35mm

ASR433.92E



RoHS
Compliant

STANDARD SPECIFICATIONS:

CHARACTERISTICS		UNIT	MIN.	TYP.	MAX.
Center Frequency F_0		MHz	433.845	433.920	433.995
Tolerance from F_0		KHz		± 75	
Insertion Loss		dB	-	1.3	2.0
Quality Factor	Unloaded	-		10,500	
	50 Ω loaded			1,450	
Temperature Stability	Turnover Temperature	$^{\circ}\text{C}$	25	40	55
	Turnover Frequency	KHz		F_c	
	Freq. Temp. Coefficient	ppm/ $^{\circ}\text{C}^2$		0.037	
Frequency Aging		ppm/year		± 10	
DC Insulation Resistance		M Ω	1.0		
RF Equivalent RLC Model	Motional Resistance R_1	Ω		16	26
	Motional Inductance L_1	μH		61.724	
	Motional Capacitance C_1	fF		2.1817	
	Shunt Capacitance C_0	pF	1.9	2.2	2.5
Operating temp.		$^{\circ}\text{C}$	-40 $^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$		
Storage temp.		$^{\circ}\text{C}$	-45 $^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$		
Max. Rating	DC voltage	V	± 10		
RF Power Dissipation		dBm	10		


Data measured with: Source Impedance: $Z_s=50\Omega$, Load Impedance: $Z_L=50\Omega$, $T_A=25^{\circ}\text{C}$
Electrostatic Sensitive Device. Handle with precaution.

MARKING:


- 433.92 (433.92 Frequency in MHz)
- AR ZYX (ZY: Date code Z for month from A to L; Y for year, i.e. 4 for 2004
X: Traceability code)

PIN NO.	CONNECTIONS
2	Input/Output
6	Output/Input
4 & 8	Case Ground
1,3,5,7	N/C


FREQUENCY RESPONSE:



TEST CIRCUIT:



OUTLINE DRAWING:



ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO 9001:2008
CERTIFIED



30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[ASR433.92E-T](#)