



Designed to facilitate telecom and datacom installations, these glow rods are the perfect tool for pushing and pulling cables in low light applications. These glow rods feature the following:

- Luminescent flexible fiberglass rods glow in the dark while providing a splinter-free experience
- Steel connectors of the rods have flats to tighten down each connection for greater stability than the competition
- The steel connectors also have standard 8-32 threads, compatible with most other glow rods
- Pull strength of each rod is rated up to 500 lb

#### RDG-15A - 15 ft Glow Rod Kit+, 3/16" Diameter

Kit Includes:

- Three 5' long x 3/16" diameter glow rods (15 ft long when assembled)
- **RDG-RP4A** Attachment Kit which contains an eyelet, ball chain, **RDG-FLW** flashlight whisk, and hook
- Reusable plastic storage tube (kit packaging)

#### RDG-30A - 30 ft Glow Rod Kit+, 3/16" Diameter

Kit Includes:

- Six 5' long x 3/16" diameter glow rods (30 ft long when assembled)
- **RDG-RP4A** Attachment Kit which contains an eyelet, ball chain, **RDG-FLW** flashlight whisk, and hook
- Reusable plastic storage tube (kit packaging)

#### RDG-RP4A - 4 Piece Glow Rod Attachment Replacement Kit+

- This replacement kit contains: 4 attachment heads: Eyelet, Ball Chain, **RDG-FLW** Flashlight Whisk, and Hook.

SPECIFICATIONS	RDG-15A	RDG-30A	RDG-RP4A	RDG-FLW
OVERALL LENGTH	15 ft (4.57 m)	30 ft (9.14 m)	N/A	N/A
INDIVIDUAL GLOW ROD LENGTH	5 ft (1.52 m)	5 ft (1.52 m)	N/A	N/A
GLOW ROD DIAMETER	3/16" (4.76 mm)	3/16" (4.76 mm)	N/A	N/A
FLEXIBILITY	Medium	Medium	N/A	N/A
SIZE-THREAD	8-32	8-32	8-32	8-32
CONNECTOR MATERIAL	Stainless Steel	Stainless Steel	Stainless Steel	N/A
ROD MATERIAL	Luminescent Fiberglass	Luminescent Fiberglass	N/A	N/A
WEIGHT	1.18 lb (0.535 kg)	1.18 lb (0.535 kg)	0.117 lb (53 g)	0.037 lb (17 g)
WEIGHT PER ROD	0.160 lb (0.0726 kg)	0.160 lb (0.0726 kg)	N/A	N/A
BATTERIES	CR1220	CR1220	(2) CR1220	x2 CR1220 3V Lithium Batteries
UPC #	811490014121	811490014244	811490010888	811490019997

**MADE FOR LIFE®**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[RDG-15A](#) [RDG-30A](#) [RDG-RP4A](#)