


SDC-3166

Jonard's Cabinet Slotted Screwdrivers are made with an S2 steel shank with a chrome finish for exceptional strength and long life. Our Cabinet Slotted Screwdrivers feature the following:

- Internal shank flanges to prevent the handle from slipping
- Black oxide finished tip to prevent corrosion and magnetized to hold fasteners for easy removal and installation
- Tip is cabinet slotted for easier access to hard-to-reach places
- Ergonomically designed handle for greater comfort and torque
- End of the handle is marked to be easily identifiable while stored

SPECIFICATIONS	SDC-144	SDC-3163	SDC-3166	SDC-3810	SDC-5166
HEAD TYPE	Cabinet Slotted	Cabinet Slotted	Cabinet Slotted	Cabinet Slotted	Cabinet Slotted
CABINET SLOTTED SIZE	1/4" (6.35mm)	3/16" (4.76mm)	3/16" (4.76mm)	3/8" (9.52mm)	5/16" (7.93mm)
SHANK LENGTH	4" (101.6mm)	3" (76.2mm)	6" (152.4mm)	10" (254mm)	6" (152.4mm)
SHANK MATERIAL	S2 Steel	S2 Steel	S2 Steel	S2 Steel	S2 Steel
FINISH	Chrome, Black Oxide Tip	Chrome, Black Oxide Tip	Chrome, Black Oxide Tip	Chrome, Black Oxide Tip	Chrome, Black Oxide Tip
HANDLE	Rubberized Cushion Grip	Rubberized Cushion Grip	Rubberized Cushion Grip	Rubberized Cushion Grip	Rubberized Cushion Grip
STANDARDS	ASME B107.600/ ANSI ISO 2380	ASME B107.600/ ANSI ISO 2380	ASME B107.600/ ANSI ISO 2380	ASME B107.600/ ANSI ISO 2380	ASME B107.600/ ANSI ISO 2380
OVERALL LENGTH	8-11/32" (212mm)	6-3/4" (171mm)	9-3/4" (248mm)	14-3/8" (365mm)	10-3/8" (264mm)
WEIGHT	0.324 lbs (146.97g)	0.193 lbs (87.54g)	0.221 lbs (100.24g)	0.507 lbs	0.413 lbs
UPC NO.	811490015005	811490014985	811490014992	811490015258	811490015265

MADE FOR LIFE®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Jonard Industries:

[SDC-3166](#) [SDC-144](#) [SDC3163](#) [SDC-5166](#) [SDC-3810](#)