



Rechargeable Tactical Flashlight SOL-F1



- Constructed with anodized aircraft-grade aluminum material
- Zoomable head design allows for adjustable beam intensity
- At Full Zoom, a crosshair indicator appears for perfect sighting
- Side work light provides wide area of illumination and doubles as emergency flare when switched to red light setting. Can also be set to flash
- Magnetic base attaches to metallic racks or other metallic objects
- IPX4 rated for dust and water resistance
- Powered by a rechargeable Li-ion battery for up to 4 hours at max power
- Convenient charge indicator clearly shows charge level
- USB-C port for charging the flashlight, and USB-A port for charging other rechargeable devices using the flashlight's battery

SOL-H1 Rechargeable LED Flex Headlight

- Dual functionality with wide beam and spotlight features
- 230° beam angle for extreme visibility and coverage
- The spotlight is a high-powered precise focused beam
- Built-in motion sensor allows you to wave your hand to turn the light on & off
- Powered by state-of-the-art Poly-ion rechargeable battery for long life
- Adjustable headband ensures a comfortable fit for all head sizes
- Water resistant to withstand unpredictable weather conditions
- Made with high-quality silicon material for durability and unmatched flexibility



Ultra Bright Jobsite LED Headlamp SOL-H2

- Motion sensor can turn the light on or off by simply waving your hand
- Ultra-bright LEDs provide up to 300 lm of brightness
- Articulating case allows for lighting direction change
- Anti-slip adjustable headband ensures a comfortable fit for all head sizes
- Rated to IP54 for dust and water resistance
- Made with high-quality silicon material for enhanced durability and flexibility
- Includes (3) AAA Batteries (required for use)



SOL-W1 Rechargeable 360° Pivoting Worklight

- Powerful 400 lm brightness
- Front light doubles as red warning light indicator with flashing flare function
- High-capacity 1800 mAh Li-ion battery
- 180° adjustable base for flexible positioning and optimal lighting angles
- 360° rotating head for complete control and light coverage
- USB charging port with charger indicator light for convenience
- Designed for both indoor & outdoor conditions with IP44 rating
- Equipped with 3 magnets built into the stand
- Spring-loaded carabiner integrated into the stand
- USB-C port for charging the flashlight, and USB-A port for charging other rechargeable devices using the flashlight's battery



MADE FOR LIFE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Tools:](#)

[SOL-F1](#) [SOL-H1](#) [SOL-W1](#) [SOL-H2](#)