



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES :

1. MILLIMETERS ARE IN [].
2. QTY. 1 PER STANDARD PKG.
3. VISIT www.Panduit.com TO VIEW LEGEND IMAGES.



PART NUMBER	"A" +/- .050 WIDTH in. [mm]	"B" +/- .050 HEIGHT in. [mm]
PRS0310	3.50 [88.9]	10.00 [254.0]
PRS0710	10.00 [254.0]	7.00 [177.8]
PRS0910		9.00 [228.6]
PRS1007	7.00 [177.8]	10.00 [254.0]
PRS1014	14.00 [335.6]	
PRS1209	9.00 [228.6]	12.00 [304.8]
PRS1410	10.00 [254.0]	14.00 [335.6]
PRS1420	20.00 [508.0]	

							TITLE RIGID SAFETY SIGN – PRS					
							CUSTOMER DRAWING					
							ITEM REVISION NAME I00824CB/03			PANDUIT		
							DATASET FILE NAME I00824CB_DC_C10977/03C					
2	2/16/15	RVU	SEWH	JHAC	UPDATE TOLERANCES. ADD DIM'S ON HOLES.	GAECN02343	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .075 [1.90] .xxx ± .020 [.508] .xx ± .050 [1.27] ANGLES ± THIRD ANGLE PROJECTION					
1	5/16/12	RVU			ADD PRS1014 AND PRS1007 TO THE TABLE. PRS1410, WIDTH FOR 10.00 WAS 14.00. HEIGHT FOR 14.00 WAS 10.00. UPDATE ON NOTE 2.	6791	MATERIAL: GMPE1 RIGID POLYETHYLENE					
0	12/16/11	RVU			DRAWING RELEASE.	6808	DRAWING NUMBER: C10977					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							RVU	12/16/11	MSAD	NTS		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PRS0710BYEL](#) [PRS0710B430](#) [PRS0710B364](#) [PRS0710W104](#) [PRS0710D68](#) [PRS0710W67](#) [PRS1420C442](#)
[PRS1209B317](#) [PRS0710C98](#) [PRS0710C442](#) [PRS0710BWHT](#) [PRS1420D75](#) [PRS0710D72](#) [PRS0910D453](#)
[PRS0310F319](#) [PRS0710C97](#) [PRS0710B251](#) [PRS0710D440](#) [PRS0710C96](#) [PRS0710N443](#) [PRS0710N105](#)
[PRS1014D7346](#) [PRS1014D7345](#)