



ROLL OF TETHERS ON SPOOL (INCLUDED)  
SCALE 1:4

- NOTES:
1. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
  2. DIMENSIONS IN [ ] ARE METRIC.
  3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
  4. PACKAGED WEIGHT: 1.5 LB
  5. PRIMARY MATERIAL: ADHESIVE BACKED PAPER
  6. PART DESCRIPTION : 2FT LENGTH, 1 INCH WIDE, PACKAGED ON A SPOOL.
  7. QUANTITY = 200 TETHERS PER ROLL
  8. USE: EACH TETHER TO BE TORN FREE FROM THE ROLL, AT A PERFORATION. THE REMOVEABLE LINER IS SEGMENTED TO ALLOW A SMALL AREA OF ADHESIVE TO BE EXPOSED, AT EACH END OF THE TETHER. ONCE EXPOSED, THE ADHESIVE IS USED TO ATTACH THE TETHER TO THE BACK-SIDE OF THE APPLICATOR MEDIA (FREE END). THE OTHER END OF THE TETHER IS ATTACHED TO A REWIND SPOOL (PRINTING), OR TAKE-UP SPINDLE (APPLYING).
  6. TOLERANCES: ±0.050", UNLESS INDICATED OTHERWISE.

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN	
		PRINT	
		DAE	
PART NUMBER			
PLA-T100X2400			
TITLE			
TETHER FOR USE WITH LABEL APPLICATOR			
CUSTOMER DRAWING			
ITEM REVISION NAME		00129EHC/02	
DATASET FILE NAME		00129EHC_DC/02A	
		THIRD ANGLE PROJECTION	
MATERIAL		ADHESIVE - BACKED PAPER	
DRAWN BY		ARHA	
DATE		10/30/20	
CHK		ALP	
SCALE		NTS	
DRAWING NUMBER		00129EHC - DC	
SHEET 1 OF 1		SIZE B	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	10/30/20	ARHA	ALP	KJM	INITIAL RELEASE	GAECN05782

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PLA-T100X2400](#)