



| NOMINAL DUCT SIZE (W) | C in (mm) | TC in (mm) | HC in (mm) |
|-----------------------|--------------|------------|------------|
| .5 | .69 (17.5) | .040 (1.0) | .230 (5.8) |
| .75 | .94 (23.8) | .050 (1.3) | .240 (6.1) |
| 1 | 1.25 (31.8) | .060 (1.5) | .350 (8.9) |
| 1.5 | 1.75 (44.5) | " | " |
| 2 | 2.25 (57.2) | " | " |
| 2.5 | 2.75 (69.9) | " | " |
| 3 | 3.25 (82.6) | .065 (1.6) | .370 (9.4) |
| 4 | 4.25 (108.0) | " | " |
| 6 | 6.25 (158.8) | .080 (2.0) | " |

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- DIMENSIONS IN PARENTHESIS ARE METRIC.

PART NO. SYSTEM
COVER EXAMPLE
TYPE C 1.5 LG 6
WIDTH
COLOR
LENGTH (ft)

| | | | |
|---|----------|---|------------|
| CAD FILENAME/LAYERS | | D34518BA_PVC_COVER_02A | |
| <h1>PANDUIT</h1> CORP. TINLEY PARK, ILLINOIS | | | |
| WIRING DUCT COVER FOR DUCT TYPES "S", "D", "E", "F", "FS", AND "G" CUSTOMER DRAWING | | | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: | | UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION. | |
| (.X) : (.XXX) : (.XX) : ANGLES : | | NONE | |
| 2 | 8-24-01 | JCST | JKG |
| D. CHANGED TOLERANCE C. MADE "C" A REFERENCE DIMENSION | | 34518-17 | JKG |
| 1 | 2/11/00 | JHNU | HIW |
| B. .18 WAS .125/ 4.5 WAS 3.2 A. REV'D TITLE: ADDED FS AND G DUCT TYPE | | 34518-17 | HIW |
| R | 10-29-93 | DW | CEF |
| RELEASED TO PRODUCTION. | | 34518-17 | CEF |
| REV | DATE | BY | CHK |
| DESCRIPTION | | ECN | R CUST SUP |
| DRAWN BY DW | | MAT'L: POLYVINYL CHLORIDE | |
| DATE 10-29-93 | | DRAWING NO. 34518-17 | |
| CHK'D CEF | | Dwg SIZE A | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[C1BL6](#) [C1.5LG6](#) [C2IB6](#) [C3BL6](#) [C2LG6](#) [C3LG6](#) [C.75LG6](#) [C1WH6](#) [C.5LG6](#) [C4LG6](#) [C1LG6](#) [C.5WH6](#) [C.75WH6](#)
[C1.5WH6](#) [C2.5LG6](#) [C2.5WH6](#) [C2WH6](#) [C3WH6 \(6 FT LENGTH\)](#) [C4WH6](#) [C6LG6](#) [C1LG6-F](#) [C1.5LG6-F](#) [C1.5BL6](#)
[C1IB6](#) [C3IB6](#) [C4IB6](#) [C2.5BL6](#) [C3LG6-F](#) [C.75BL6](#) [C.75LG6-F](#) [C.75WH6-F](#) [C.5LG6-F](#) [C.5WH6-F](#) [C1.5IB6](#)
[C6WH6](#) [C3WH6](#)