

Exploded view diagram of the 1000mm long, 100mm high extruded aluminum profile (Type 1000). The diagram shows the profile with various mounting brackets and fasteners. Dimensions include a total length of 22.59 inches [573.9] and a mounting bracket height of 1.62 inches [41.3]. A triangle with the letter 'B' is shown above the length dimension.



1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. THE FIBER ROUTING 4-POST RACK BRACKET ALLOWS FOR 5/8" THREADED ROD (NOT INCLUDED) TO BE MOUNTED TO THE TOP OF A PANDUIT 4-POST RACK (CMR4P84).
3. THE FIBER ROUTING 4-POST RACK BRACKET KIT INCLUDES:
 - ONE (1) STRUT METAL FRAMING CHANNEL,
 - TWO (2) SQUARE NUT PEM SELF-CLINCHING ASSEMBLIES,
 - TWO (2) STRUT METAL FRAMING CHANNEL U-WASHERS
 - 7/16" HOLE,
 - TWO (2) 3/8" HELICAL SPRING LOCKWASHERS,
 - TWO (2) 3/8-16x2 1/2" HEX HEAD CAP SCREWS,
 - ONE (1) STRUT METAL FRAMING CHANNEL U-WASHER
 - 1 1/16" HOLE,
 - ONE (1) 5/8" HELICAL SPRING LOCKWASHER,
 - ONE (1) 5/8-11 HEAVY HEX NUT,
 - ONE (1) 5/8-11 CHANNEL NUT WITHOUT SPRING
4. FINISH COLOR: BLACK (EXCEPT FOR HARDWARE).
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.

											PANDUIT CORP			TINLEY PARK, ILLINOIS		
											FIBER ROUTING 4-POST RACK BRACKET			FIBER ROUTING 4-POST RACK BRACKET		
											- 5/8" THREADED ROD (FR4PRB58)			- 5/8" THREADED ROD (FR4PRB58)		
											CUSTOMER DRAWING			CUSTOMER DRAWING		
											UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:			UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
-	-----	---	--	C. REVISED PART WEIGHT.		-----	--	--			(.X) ± (.XXX) ± (.XX) ±.03 (.8) ANGLES ±					
1	7-10-07	MSO	RN	B. REVISED PART GEOMETRY. A. REVISED DRAWING TITLE.		38780-10	RN	RN			DRAWN BY	MSO		MAT'L:	SCALE	
R	5-18-04	MSO	RPA	RELEASED TO PRODUCTION		38780-10	RN	RN			DATE	5-18-04		STEEL		DRAWING NO.
REV	DATE	BY	CHK	DESCRIPTION		ECN	-	R	CUST	SUP	GMBH	CHK'D	RPA		38780-10	
															A	
															SIZE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[FR4PRB58](#)