



Strain Relief Bar with Clips

- Mounts to the rear of standard EIA 19" racks behind each patch panel
- Supports 24 cables with hinged dual clips and provides bend radius protection
- Each adjustable clip can hold up to two cables; accommodates cable diameter range from 0.170" – 0.330" (4.3mm – 8.4mm)
- Provides superior aesthetics in cable management



PATENT
PENDING

Part Number	Part Description	No. of Rack Spaces^	Std. Pkg. Qty.	Std. Ctn. Qty.
SRBWCY	Strain relief bar with integrated adjustable clips; supports, manages, and provides bend radius protection for up to 24 cables in 1 RU.	1	1	10

^One rack space = 1.75" (44.45mm).



Strain Relief Bars for Patch Panels

- Mount to standard EIA 19" racks
- Ideal for standard density patch panels (24 ports per RU)
- Tak-Ty® Hook & Loop Cable Ties can be used for additional cable management



SRBM19BLY



SRBCT



SRB19BLY



SRB19D5BL



SRB19D7BL



SRBS19BL-XY



SRBBRKT

Part Number	Part Description	Std. Pkg. Qty.	Std. Ctn. Qty.
-------------	------------------	----------------	----------------

Strain Relief Bar/Manager

SRBM19BLY	Strain relief bar with six Tak-Ty® Hook & Loop Cable Ties; supports, manages, and provides proper bend radius protection for up to 72 cables.	1	10
SRBCT	Strain relief bar includes 24 cable ties to secure cable to each individual slot for additional stability; supports, manages, and provides proper bend radius protection.	1	10

Extended Strain Relief Bar

SRB19BLY	Strain relief bar extends 2" off the rack; supports, manages, and provides proper bend radius protection.	1	10
----------	---	---	----

Deep Strain Relief Bar

SRB19D5BL	Strain relief bar extends 5" off the rack; supports, manages, and provides proper bend radius protection.	1	10
SRB19D7BL	Strain relief multi-depth bar extends 7" off the rack; supports, manages, and provides proper bend radius protection. Ideal for use with Category 6A copper cabling installations.	1	10

Straight Strain Relief Bar

SRBS19BL-XY	Strain relief bar; supports, manages, and provides proper bend radius protection.	10	—
-------------	---	----	---

Strain Relief Bar Brackets

SRBBRKT	Quick release brackets for strain relief bars; convert conventional screw mounting to quick release mounting/removal.	1	10
---------	---	---	----

#12-24 mounting screws included.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[SRBWCY](#) [SRBM19BLY](#)