


Adhesive Lined Grommet Edging

- Adhesive ensures product stays in place
- Slotted wall product used on irregularly shaped and round panel holes
- Solid wall product used on straight panels
- Highly flexible material
- General purpose material for use up to 122°F (50°C)
- Flame retardant material for use up to 167°F (75°C)
- Packaged on a 100' (30.5m) reel for easy handling and dispensing of product



Part Number	Width		Height		Material	Color	Panel Thickness Range		Std. Pkg. Qty.
	In.	mm	In.	mm			In.	mm	

Slotted Adhesive Lined

GEE62F-A-C	0.13	3.3	0.16	4.1	Polyethylene	Natural	0.036 – 0.062	0.9 – 1.6	1
GEE62F-A-C0	0.13	3.3	0.16	4.1	Weather Resistant Polyethylene	Black	0.036 – 0.062	0.9 – 1.6	1
GEE99F-A-C	0.17	4.3	0.19	4.7	Polyethylene	Natural	0.062 – 0.099	1.6 – 2.5	1
GEE99F-A-C0	0.17	4.3	0.19	4.7	Weather Resistant Polyethylene	Black	0.062 – 0.099	1.6 – 2.5	1
GEE144F-A-C	0.21	5.4	0.22	5.6	Polyethylene	Natural	0.099 – 0.144	2.5 – 3.7	1
GEE144F-A-C0	0.21	5.4	0.22	5.6	Weather Resistant Polyethylene	Black	0.099 – 0.144	2.5 – 3.7	1

Solid Adhesive Lined – Use on straight edges only

GES62F-A-C	0.13	3.3	0.16	4.1	Polyethylene	Natural	0.036 – 0.062	0.9 – 1.6	1
GES62F-A-C0	0.13	3.3	0.16	4.1	Weather Resistant Polyethylene	Black	0.036 – 0.062	0.9 – 1.6	1
GES99F-A-C	0.17	4.3	0.19	4.7	Polyethylene	Natural	0.062 – 0.099	1.6 – 2.5	1
GES99F-A-C0	0.17	4.3	0.19	4.7	Weather Resistant Polyethylene	Black	0.062 – 0.099	1.6 – 2.5	1
GES144F-A-C	0.21	5.4	0.22	5.6	Polyethylene	Natural	0.099 – 0.144	2.5 – 3.7	1
GES144F-A-C0	0.21	5.4	0.22	5.6	Weather Resistant Polyethylene	Black	0.099 – 0.144	2.5 – 3.7	1

Slotted

GEE36FR-CY*	0.11	2.7	0.12	3.0	Flame Retardant Polyethylene	Natural	0.026 – 0.036	0.7 – 0.9	1
GEE62FR-CY*	0.13	3.3	0.16	4.1	Flame Retardant Polyethylene	Natural	0.036 – 0.062	0.9 – 1.6	1
GEE99FR-CY*	0.17	4.3	0.19	4.7	Flame Retardant Polyethylene	Natural	0.062 – 0.099	1.6 – 2.5	1
GEE144FR-CY*	0.21	5.4	0.22	5.6	Flame Retardant Polyethylene	Natural	0.099 – 0.144	2.5 – 3.7	1

Solid – Use on straight edges only

GES36FR-CY*	0.11	2.7	0.12	3.0	Flame Retardant Polyethylene	Natural	0.026 – 0.036	0.7 – 0.9	1
GES62FR-CY*	0.13	3.3	0.16	4.1	Flame Retardant Polyethylene	Natural	0.036 – 0.062	0.9 – 1.6	1
GES99FR-CY*	0.17	4.3	0.19	4.7	Flame Retardant Polyethylene	Natural	0.062 – 0.099	1.6 – 2.5	1
GES144FR-CY*	0.21	5.4	0.22	5.6	Flame Retardant Polyethylene	Natural	0.099 – 0.144	2.5 – 3.7	1

*Flame retardant products are manufactured from a material that is rated UL 94V-0 and RoHS compliant.

‡Reel packaging may contain splices. Order the number of reels required.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[GES99F-A-C0](#)