

# NetKey® Fiber Optic Adapter Modules

## specifications

LC, SC and ST fiber optic adapters have integrated panel retention clips and are TIA/EIA-604 compliant or compatible. Each simplex adapter will connect one connector pair in one module space and each duplex adapter will connect two LC connector pairs in one module space. LC fiber optic adapters and adapter modules include phosphor bronze split sleeves for OM1 or OM2 multimode applications or zirconia ceramic split sleeves for OM3 multimode or singlemode applications.



## technical information

<b>Standards requirements:</b>	All adapters meet or exceed TIA/EIA-455-21 and TIA/EIA-568-C.3 requirements: LC: TIA/EIA-604 FOCIS-10 compatible SC: TIA/EIA-604 FOCIS-3 compliant ST: TIA/EIA-604 FOCIS-2 compatible
<b>Split sleeve material:</b>	Zirconia ceramic: OM3 multimode adapters, OS1/OS2 singlemode adapters Phosphor bronze: OM1 and OM2 multimode adapters
<b>Insertion loss:</b>	Supports the performance of connectors/patch cords
<b>Return loss:</b>	Supports singlemode and multimode connector polish performance

## key features and benefits

<b>Integrated panel retention clips:</b>	No metal clips to become bent, damaged or lost; simplex adapter clips automatically adjust for FOCIS-3 or FOCIS-10 panel thickness variations for improved mounting
<b>Short flange design (LC and SC only):</b>	Improved modularity and higher density usage
<b>Choice of phosphor bronze or zirconia ceramic split sleeves:</b>	Provides an adapter split sleeve material option to fit specific network requirements
<b>Adapters available in keystone modules:</b>	System flexibility; modules are interchangeable with keystone outlets, boxes, and patch panels
<b>Adapters and modules available in multiple colors:</b>	Allows color-coding for network segregation

## applications

- Can be used with keystone telecommunications room products and work area outlets
- Provides a rugged solution for LANs, public networks and fiber-to-the-desk applications

# PANDUIT®

DATA SHEET

### NetKey® LC Duplex Fiber Optic Adapter Module

**LC duplex adapter with phosphor bronze split sleeve:** NKDLCM\*\*

**LC duplex adapter with zirconia split sleeve:** NKDLCMZ\*\*

### NetKey® SC Simplex Fiber Optic Adapter Module

**SC simplex adapter with phosphor bronze split sleeve:** NKSCM\*\*

**SC simplex adapter with zirconia split sleeve:** NKSCMZ\*\*

### NetKey® ST Fiber Optic Adapter Modules

**ST adapter with phosphor bronze split sleeve:** NKSTM\*\*


### NetKey® Module Multimedia Panel – 6 port

**Unloaded panel accepts up to six NetKey® Modules:** FKP6

\*\* Substitute for module color

BL = Black  
EI = Electric Ivory  
IG = International Gray  
IW = Off White  
WH = White  
AQ = Aqua

# NetKey® Fiber Optic Adapter Modules




## NKDLCM\*\*

Shown without dust caps

## NKSCM\*\*

Shown without dust caps



## NKSTM\*\*

\*\* Substitute for module color BL = Black, EI = Electric Ivory, IG = International Gray, IW = Off White, WH = White

### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario Phone: 800.777.3300	PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200	PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575	PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000	PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000	PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020
---	---	---	--	--	---

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)



Visit us at [www.panduit.com/ia](http://www.panduit.com/ia)  
[iai@panduit.com](mailto:iai@panduit.com)

© 2016 Panduit Corp.  
ALL RIGHTS RESERVED.  
NKDS20--WW-ENG  
11/11/2016

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[NKDLCMZIW](#)