



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


DUPLEX SC TO SC FIBER OPTIC PATCH CORD

PANDUIT PART NUMBER	LENGTH (**) M = METERS	CABLE				SC CONNECTOR		
		FIBER TYPE	COUNT	RATING	COLOR	BOOT COLOR	MAX. IL	MIN. RL
NKF6GR02S-SM**	01, 02, 03, 05, 10	62.5/125 OM1	DUPLEX 3.0mm ZIPCORD	RISER (OFNR)	ORANGE	WHITE	0.75dB	26dB
NKF5GR02S-SM**		50/125 OM2				BLACK		
NKFXGR02S-SM**		50/128 OM3			AQUA			
NKF9GR02S-SM**		SINGLEMODE OS1			YELLOW	WHITE		40dB
NKF6GL02S-SM**		62.5/125 OM1		LOW SMOKE ZERO HALOGEN (LSZH)	ORANGE	WHITE	0.75dB	26dB
NKF5GL02S-SM**		50/125 OM2				BLACK		
NKFXGL02S-SM**		50/128 OM3			AQUA	AQUA		
NKF9GL02S-SM**		SINGLEMODE OS1			YELLOW	WHITE		40dB

NETKEY FIBER OPTIC PATCH CORD  
DUPLEX SC TO SC CONFIGURATION  
CUSTOMER DRAWING



**PANDUIT**™  
CORP.  
TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES  
UNLESS OTHERWISE SPECIFIED.  
DIMENSIONAL TOLERANCES ARE:  
(.X) ±.03 | (.XXX) ±.010 | (.3) ±.03 | (.8) ANGLES

DRAWING FILENAME  
M01302CS\_DC/00A

SCALE  
NONE

DRAWN BY  
EFK

MATERIAL

PART NO. NKF\*GR02S-SM\*\*  
NKF\*GL02S-SM\*\*

DATE  
12-14-09

DRAWING NO.  
01302-53  
SHEET 2 OF 2  
SIZE  
A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	12-14-09	EFK		RELEASED TO PRODUCTION	01302-53				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Panduit:

[NKFXGR02S-SM03](#) [NKF6GR02S-SM01](#) [NKF9GR02S-SM01](#) [NKF5GR02S-SM03](#) [NKF5GR02S-SM01](#)  
[NKF6GR02S-SM10](#) [NKFXGR02S-SM10](#) [NKF5GR02S-SM05](#) [NKF9GR02S-SM02](#) [NKF9GR02S-SM03](#) [NKF6GR02S-](#)  
[SM03](#) [NKF5GR02S-SM02](#) [NKF9GR02S-SM10](#) [NKFXGR02S-SM01](#) [NKF6GR02S-SM02](#) [NKF5GR02S-SM10](#)  
[NKFXGR02S-SM02](#)