

Component Labels for Mini-Com® Classic Series Faceplate Kits



Suggested Label Solutions for TIA/EIA-606-A Compliance

Faceplate Part Number	Laser/Ink Jet Desktop Printer Label	TDP43ME Thermal Transfer Desktop Printer Label	PanTher™ LS8E Hand-Held Printer Label	Cougar™ LS9 Hand-Held Printer Label
All CFPS4 Parts	C125X030FJJ	C125X030YPT	C125X030FJC	T031X000FJC-BK

For complete labeling solutions and product information, reference charts on pages O.1 – O.22.

Mini-Com® Ultimate ID® Executive Series Faceplates

- Ultimate ID® components are part of a complete system for identification designed to efficiently support TIA/EIA-606-A standard labeling requirements
- Accept Mini-Com® Modules for STP and UTP, fiber optic, and audio/video, which snap in and out for easy moves, adds, and changes
- Raised rail design for aesthetic appeal
- Supplied with color coordinated screw cover and clear station and port label covers, labels sold separately

- Can be clearly identified with the PanTher™ LS8E or Cougar™ LS9 Hand-Held Thermal Transfer Printers
- Non-adhesive computer printable label sheets for desktop printers and write-on labels available
- Replacement screw covers and label covers available
- Optional icons available



UICFPSE2IW



UICFPSE4IW



UICFPSE6IW



UICFPSE8IW-2G



UICFPHSE2IW



UICFPHSE4IW

Part Number	Part Description	Color‡	Labels Required*	Std. Pkg. Qty.	Std. Ctn. Qty.
UICFPSE2IW	Single gang, vertical sloped faceplate holds up to two Mini-Com® Modules.	Off White	One 1-Port One 2-Port	1	10
UICFPSE4IW	Single gang, vertical sloped faceplate holds up to four Mini-Com® Modules.	Off White	One 1-Port Two 2-Port	1	10
UICFPSE6IW	Single gang, vertical sloped faceplate holds up to six Mini-Com® Modules. Requires minimum 1.9" wide in-wall box or wallboard adapter for proper installation.	Off White	One 1-Port Two 3-Port	1	10
UICFPSE8IW-2G	Double gang, vertical faceplate holds up to eight Mini-Com® Modules.	Off White	Four 4-Port	1	10
UICFPHSE2IW	Single gang, horizontal sloped faceplate holds up to two Mini-Com® Modules.	Off White	One 1-Port One 2-Port	1	10
UICFPHSE4IW	Single gang, horizontal sloped faceplate holds up to four Mini-Com® Modules.	Off White	One 1-Port One 4-Port	1	10

‡For other colors replace suffix IW (Off White) with EI (Electric Ivory), WH (White), IG (International Gray), or BL (Black).

All faceplates supplied with mounting screws.

*Ultimate ID® Labels can be found on pages O.11 and O.19 of SA-NCCB51.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[UICFPSE4IW](#) [UICFPSE8IW-2G](#) [UICFPSE6IW](#) [UICFPHSE4IW](#) [UICFPSE2IW](#)