

Electronic housing - ME 45 UT TBUS BU - 2713997

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Component housing, length: 99 mm, with vents, Lower part, Cross connection: DIN rail bus connector, color: blue, width: 45 mm, height: 114.5 mm, number of positions cross connector: 5

Your advantages

- ✓ Item is from the ME product range
- ✓ Tool-free mounting
- ✓ Available in overall widths from 12.5 mm to 90 mm, modular extension is possible
- ✓ Inflammability class V0 according to UL 94
- ✓ Variety of connection technologies
- ✓ Can be mounted on the DIN rail
- ✓ Optional bus connector that is either integrated or mounted on the DIN rail

RoHS

Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 914455
GTIN	4017918914455

Technical data

General

Housing type	Component housing
Housing material	PA 6.6
Color (RAL)	blue (5015)

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C (depending on power dissipation)

Dimensions

Length	99 mm
--------	-------

Electronic housing - ME 45 UT TBUS BU - 2713997

Technical data

Dimensions

Height	114.5 mm
Width	45 mm
Depth	99 mm

Technical data

Power dissipation without gap	8.2 W
Power dissipation with 20 mm gap	16.5 W
Number of positions	32
	8

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 240868
---------------	---	---	---------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2713997](#)