

Marking plotter - PLOTMARK - 0804499

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Marking plotter, weight: 8 kg, width: 480 mm, height: 155 mm, color: silver



Product Description

Plotting area: 422 x 305 mm, material height: 10.5 mm, plotting speed: 0.04 m/sec, data buffer: 16 MB, resolution: 0.01 mm, repeat accuracy: 0.05 mm

Your advantages

- ✓ The plotter is controlled with the CLIP PROJECT software
- ✓ The pens are removed and deposited automatically
- ✓ Easily operated with just a few buttons
- ✓ The plotter can be connected to the computer quickly and easily via the Centronics or USB interface
- ✓ An automatic marking preparation function ensures optimum marking results right from the first character
- ✓ During long intervals, the plotter pens are stored safely in a pen station

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 381190
GTIN	4055626381190

Technical data

General

Interface	USB 2.0
Weight	8 kg

Dimensions

Length	690 mm
Height	155 mm
Width	480 mm

Connection data

Marking plotter - PLOTMARK - 0804499

Technical data

Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC
Additional text	50 Hz ... 60 Hz

Classifications

eCl@ss

eCl@ss 10.0.1	19140201
eCl@ss 4.0	24010402
eCl@ss 4.1	24010402
eCl@ss 5.0	19020200
eCl@ss 5.1	19020200
eCl@ss 6.0	19140200
eCl@ss 7.0	19140201
eCl@ss 8.0	19140201
eCl@ss 9.0	19140201

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761

UNSPSC

UNSPSC 6.01	43162505
UNSPSC 7.0901	43233410
UNSPSC 11	43162505
UNSPSC 12.01	43233410
UNSPSC 13.2	43233410

Accessories

Accessories

Magazine

Magazine insert - CMS-P1-M/ZB - 5144699



Plastic magazines for CMS-P1-PLOTTER and PLOTMARK. For accommodating 22 zack marker strips

Marking plotter - PLOTMARK - 0804499

Accessories

Magazine insert - CMS-P1-M/ZBF - 5144709



Plastic magazines for CMS-P1-PLOTTER and PLOTMARK. For accommodating 26 flat zack marker strips or ZBN strips

Magazine insert - CMS-P1-M/ZBM - 5144660



Plastic racks for CMS-P1 plotter. Accepts 2 zack marker sheets

Magazine insert - CMS-P1-M/ZBFM - 5144686



Plastic magazine for CMS-P1 plotter. accepts 3 flat Zack marker sheets

Magazine insert - CMS-P1-M/SS-ZB - 5144712



Plastic magazine for CMS-P1 plotter. Accepts 22 contactor label zack marker strips

Magazine insert - CMS-P1-M/PAB - 5144741



Plastic magazine for CMS-P1 plotter. Accepts 4 up to 6 PABA marker bars

Marking plotter - PLOTMARK - 0804499

Accessories

Magazine insert - CMS-P1-M/BN-ZB - 5144725



Plastic magazine for CMS-P1 plotter. Accepts 30 marker pins ZB strips

Magazine insert - CMS-P1-M/GPE - 5144754



Plastic magazine for CMS-P1 plotter. For accommodating 1 GPE label sheet

Magazine insert - CMS-P1-M/LBHZ - 5144738



Plastic magazine for CMS-P1 plotter. Accepts 20 strips LBHZ conductor markers

Magazine insert - CMS-P1-M/WAGO WMB - 5144767



Plastic magazine for CMS-P1 plotter. Accepts 1 WAGO WMB mats

Magazine insert - CMS-P1-M/WAGO MINI WSB - 5144864



Plastic magazine for CMS-P1 plotter. Accepts 2 WAGO WSB mini mats

Marking plotter - PLOTMARK - 0804499

Accessories

Magazine insert - CMS-P1-M/WAGO WSB 4 - 5144877



Plastic magazine for CMS-P1 plotter. Accepts 2 WAGO WSB 4 mats.

Magazine insert - CMS-P1-M/WAGO WSB 5 - 5144770



Plastic magazine for CMS-P1 plotter. Accepts 2 WAGO WSB 5 mats.

Magazine insert - CMS-P1-M/WEID MCSF 4-6 - 5144783



Plastic magazine for CMS-P1 plotter. Accepts 1 Weidmüller Multicard mat SF 4-6

Magazine insert - CMS-P1-M/WEID MCU - 5144796



Plastic magazine for CMS-P1 plotter. Accepts 1 Weidmüller Multicard mat universal

Magazine insert - CMS-P1-WMU-ADAPTER - 5144822



Adapter plate for WMU magazines, for using the universal frame CMS-WMU with the magazine inserts of the CMS-MCP 3 plotter

Marking plotter - PLOTMARK - 0804499

Accessories

Magazine insert - CMS-P1-M/BN-ZB - 5144725



Plastic magazine for CMS-P1 plotter. Accepts 30 marker pins ZB strips

Magazine insert - CMS-P1-M/ENTRELEC RC - 5144932



Plastic magazine for CMS-P1 plotter. To accommodate 2 Entrelec sheets RC55-85, RC410-810, RTC610/810/1010

Magazine insert - CMS-P1-M/GPE - 5144754



Plastic magazine for CMS-P1 plotter. For accommodating 1 GPE lable sheet

Magazine - CMS-P1-M/GPE ENGRAVING - 5145711



Magazine for CMS-P1-PLOTTER, to accommodate GPE materials, especially for the purpose of engraving

Magazine insert - CMS-P1-M/LBHZ - 5144738



Plastic magazine for CMS-P1 plotter. Accepts 20 strips LBHZ conductor markers

Marking plotter - PLOTMARK - 0804499

Accessories

Magazine insert - CMS-P1-M/MURR 400 - 5144945



Plastic magazine for CMS-P1 plotter. To accept 2 Murrplastik sheets KS 4/12, 4/18, 4/23, 4/30

Magazine insert - CMS-P1-M/MURR 401 - 5144958



Plastic magazine for CMS-P1 plotter. To accommodate 2 Murrplastik sheets, KES, KLG, KMR, KPX, KSA, KSF, KSI, KSK, KS 15x17/27/49/67, KSO, KSS, KTE, KWI, SKS, WGO, KAB

Magazine insert - CMS-P1-M/WIEL - 5144929



Plastic magazine for CMS-P1 plotter. To accept 3 Wieland sheets, type 50, 51, 60, 63, 67, 68, 69 or 80

Magazine - P1 UC-MAG 1 - 5146079



Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating UC-TM..., UC-TMN..., UC-WMC 3,1..., UC-WMTBA...

Magazine - P1 UC-MAG 2 - 5146082



Magazine, for CMS-P1-PLOTTER, for accommodating UC-WMC 4.4...

Marking plotter - PLOTMARK - 0804499

Accessories

Magazine - P1 UC-MAG 3 - 5146095



Magazine, for CMS-P1-PLOTTER, for accommodating UC-WMC 7,5...

Magazine - P1 UC-MAG 4 - 5146105



Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating UC-TMF..., UC1-TMF..., UC-WMT...

Magazine - P1 UC-MAG 5 - 5146118



Magazine, for CMS-P1-PLOTTER, for accommodating UC1-TM..., UC1U-TM...

Magazine - P1 UC-MAG 6 - 5146121



Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating UC-EMP..., UC-EMLP...

Magazine - P1 UC-MAG 7 - 5146568



Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating: UC-WMCO...

Marker pen

Marking plotter - PLOTMARK - 0804499

Accessories

Marker pen - CMS-DISPOSABLE-PEN 0,25 TR - 5146685



Marker pen, color: black

Marker pen - CMS-DISPOSABLE-PEN 0,35 TR - 5146686



Marker pen, color: black

Marker pen - CMS-PEN 0,25 - 5067815



Marker pen, incl. adapter, ink tank and reservoir, 0.25 mm nib

Marker pen - CMS-PEN 0,35 - 5067828



Marker pen, incl. adapter, ink tank and reservoir, 0.35 mm nib

Marker pen - CMS-PEN 0,50 - 5067831



Marker pen, incl. adapter, ink tank and reservoir, 0.5 mm nib

Mounting material

Marking plotter - PLOTMARK - 0804499

Accessories

Plotter accessories - CMS-P1-PENDEPOT - 5144835



4 replacement seals for the pen station of the P1 plotter and 10 prepare pen plates

Printing system accessories

Accessories - CMS-P1-PAD - 5144819



Accessories

Accessories - CMS-P1-M/ZBFM-PAD - 5144848



Accessories

Accessories - CMS-P1-M/WEID-PAD - 5144851



Accessories

Accessories - CMS-P1-M/GPE-PAD - 5144880



Accessories

Marking plotter - PLOTMARK - 0804499

Accessories

Accessories - CMS-P1-PREPLATES - 5145135



50 prepare pen plates for the pen station of the P1 plotter

Accessories - CMS-P1-M/GPE-PAD - 5144880



Accessories

Accessories - CMS-P1-PAD/SPARE - 5144893



Accessories

Cleaning set - CMS-R-SET-TR - 5146751



Cleaning set

Cleaning cartridge - CMS-R-FLUID-TR-C2 - 5146752



Cleaning cartridge, color: transparent

Marking plotter - PLOTMARK - 0804499

Accessories

Cleaning fluid - CMS-R-FLUID-TR - 5146750



Cleaning fluid, 30 ml cleaning fluid for CMS-INK-TR-C5

Ink cartridge - CMS-INK-TR-C5 - 5146684



Ink cartridge, special black ink, 5 cartridges of 1 ml each, for high demands

Additional products

Marker pen - CMS-PEN 0,25 - 5067815



Marker pen, incl. adapter, ink tank and reservoir, 0.25 mm nib

Marker pen - CMS-PEN 0,35 - 5067828



Marker pen, incl. adapter, ink tank and reservoir, 0.35 mm nib

Marker pen - CMS-PEN 0,50 - 5067831



Marker pen, incl. adapter, ink tank and reservoir, 0.5 mm nib

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0804499