

## Insert strip - ESL 24X4 - 0808231

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, Perforated and ruled, mounting type: insert, lettering field size: 24 x 4 mm, Number of individual labels: 488



### Your advantages

- ✓ Insert labels for plastic cable markers
- ✓ The material file can be downloaded under the CLIP PROJECT software under Downloads - "Software update - Marking".

RoHS

### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 10 pc                                                                                                   |
| Minimum order quantity | 10 pc                                                                                                   |
| GTIN                   | <br>4 017918 171520 |
| GTIN                   | 4017918171520                                                                                           |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 4 mm  |
| Width (a)  | 24 mm |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

#### General

|                                     |                                                 |
|-------------------------------------|-------------------------------------------------|
| Note                                | Print image may vary depending on laser printer |
| Color                               | white                                           |
| Components                          | free from silicone and halogen                  |
| Material                            | Polyester foil                                  |
| Wipe resistance                     | DIN EN 61010-1 (VDE 0411-1)                     |
| Number of individual labels         | 488                                             |
| Number of individual labels per row | 8                                               |

## Insert strip - ESL 24X4 - 0808231

### Technical data

#### General

|                       |        |
|-----------------------|--------|
| Marking mounting type | insert |
|-----------------------|--------|

#### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400629 |
| eCl@ss 4.0    | 24190200 |
| eCl@ss 4.1    | 24190200 |
| eCl@ss 5.0    | 27141100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27141100 |
| eCl@ss 7.0    | 27141137 |
| eCl@ss 8.0    | 27141137 |
| eCl@ss 9.0    | 27400629 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |
| ETIM 6.0 | EC001288 |
| ETIM 7.0 | EC001288 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131505 |
| UNSPSC 18.0   | 39131504 |
| UNSPSC 19.0   | 39131504 |
| UNSPSC 20.0   | 39131504 |
| UNSPSC 21.0   | 39131504 |

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0808231