

PCB terminal block - FKDSO 2,5 HV/3-L 7,5 GY7035 - 2201128


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



PCB terminal block, nominal current: 24 A, pitch: 7.5 mm, number of positions: 3, connection method: Push-in spring connection, mounting: Wave soldering. Article with lateral pin exit

Your advantages

- ✓ Spring-cage PCB terminal block for ME/ME MAX electronics housing
- ✓ Push-in Technology simplifies connection



Key Commercial Data

Packing unit	50 pc
GTIN	
GTIN	4046356745963


Technical data

Environmental Product Compliance


China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Drilling diagram



Diagram



Type: FKDSO 2,5 HV/...-L(R) 7,5 ...

PCB terminal block - FKDSO 2,5 HV/3-L 7,5 GY7035 - 2201128

Approvals

Approvals

Approvals

IECEE CB Scheme / VDE Gutachten mit Fertigungsüberwachung / EAC / cULus Recognized

Ex Approvals

Approval details

IECEE CB Scheme		http://www.iecee.org/	DE1-59403
Nominal voltage UN	750 V		
Nominal current IN	24 A		
mm²/AWG/kcmil	0.2-2.5		

VDE Gutachten mit Fertigungsüberwachung		http://www2.vde.com/de/Institut/Online-Service/ VDE-gepruefteProdukte/Seiten/Online-Suche.aspx	40033478
Nominal voltage UN	750 V		
Nominal current IN	24 A		
mm²/AWG/kcmil	0.2-2.5		

EAC		B.01742
-----	---	---------

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E60425-20110930
	D	B	C
Nominal voltage UN	600 V	300 V	300 V
Nominal current IN	5 A	10 A	10 A
mm²/AWG/kcmil	30-14	30-14	30-14

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2201128](#)