

Cable marker - KMV 44X9,6 - 0812007

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable marker, Stainless steel label, silver, unlabeled, can be labeled with: P1 ENGRAVING UNIT, ENGRAVING UNIT, mounting type: Assembly with cable binders, cable diameter range: 1 ... 63 mm, lettering field size: 23 x 9 mm

Your advantages

- ✓ Easy assembly with UNIFOX-CT M7,9
- ✓ Secured using stainless steel cable binders
- ✓ Cable markers for marking cables and conductors with larger cross sections
- ✓ The individual stainless steel markers are pushed onto the corresponding holders

RoHS

Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 017918 932145
GTIN	4017918932145

Technical data

Dimensions

Length (b)	44 mm
Width (a)	9.6 mm
Cable diameter	1 mm ... 63 mm

General

Color	silver
Type	Mounting set
Material	Stainless steel 304
RoHS compliant	Yes
Marking mounting type	Assembly with cable binders

Cable marker - KMV 44X9,6 - 0812007

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0812007](#)