

## DIN rail bus connectors - ME 18,8 TBUS 1,5/5 VPE1 KMGY - 2202549

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Bus connector to connect ME-IO modules on the DIN rail; suitable for ME-IO DEV-KITS; contains ME 18,8 TBUS 1,5/ 5

### Your advantages

- ✓ DIN rail connector with overall width of 18.8 mm with 5 positions (parallel)
- ✓ Up to 8 A per position can be transmitted
- ✓ Can be used up to 125 V



### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 055626 142654 |
| GTIN         | 4055626142654                                                                                           |

### Technical data

#### General

|                  |           |
|------------------|-----------|
| Housing material | Polyamide |
|------------------|-----------|

#### Ambient conditions

|                                 |                                                     |
|---------------------------------|-----------------------------------------------------|
| Ambient temperature (operation) | -40 °C ... 105 °C (dependent on the derating curve) |
|---------------------------------|-----------------------------------------------------|

#### Dimensions

|       |         |
|-------|---------|
| Width | 18.8 mm |
| Pitch | 3.81 mm |

#### Technical data

|                     |   |
|---------------------|---|
| Number of positions | 5 |
|---------------------|---|

#### Standards and Regulations

|                                        |    |
|----------------------------------------|----|
| Flammability rating according to UL 94 | V0 |
|----------------------------------------|----|

#### Environmental Product Compliance

## DIN rail bus connectors - ME 18,8 TBUS 1,5/5 VPE1 KMGY - 2202549

### Technical data

#### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

### Approvals

#### Approvals

---

Approvals

EAC

---

Ex Approvals

#### Approval details

|     |                                                                                     |         |
|-----|-------------------------------------------------------------------------------------|---------|
| EAC |  | B.01742 |
|-----|-------------------------------------------------------------------------------------|---------|

---

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2202549](#)