

Electronic housing - ME 17,5 UTG/FE KMGY - 2202704

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Component housing, length: 99 mm, without vents, Lower part, Cross connection: without bus connector, color: light gray, width: 17.5 mm, height: 114.5 mm, number of positions cross connector: not relevant

Your advantages

- Item is from the ME product range
- Tool-free mounting
- Available in overall widths from 12.5 mm to 90 mm, modular extension is possible
- Inflammability class V0 according to UL 94
- Variety of connection technologies
- Can be mounted on the DIN rail
- Optional bus connector that is either integrated or mounted on the DIN rail



Key Commercial Data

| | |
|------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 055626 170305 |
| GTIN | 4055626170305 |

Technical data

General

| | |
|------------------|-------------------|
| Housing type | Component housing |
| Housing material | Polyamide |
| Color (RAL) | light gray (7035) |

Ambient conditions

| | |
|---------------------------------|--|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
|---------------------------------|--|

Dimensions

| | |
|--------|----------|
| Length | 99 mm |
| Height | 114.5 mm |

Electronic housing - ME 17,5 UTG/FE KMGY - 2202704

Technical data

Dimensions

| | |
|-------|---------|
| Width | 17.5 mm |
| Depth | 99 mm |

Technical data

| | |
|---------------------|----|
| Number of positions | 12 |
|---------------------|----|

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2202704](#)