

## Crimping pliers - CRIMPFOX ZA 2 - 1201853

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for ferrules in accordance with DIN 46228-1: 1992-08 and DIN 46228-4: 1990-09

### Key Commercial Data

|              |                                                                                                       |
|--------------|-------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                  |
| GTIN         | <br>4 017918 017552 |
| GTIN         | 4017918017552                                                                                         |
| Sales Key    | 01                                                                                                    |

### Technical data

#### Dimensions

|            |        |
|------------|--------|
| Length (b) | 195 mm |
|------------|--------|

#### General

|                    |                           |
|--------------------|---------------------------|
| Color              | black                     |
| Compression        | Square crimp              |
| Material           | Steel with plastic handle |
| Min. cross section | 0.5 mm <sup>2</sup>       |
| Max. cross section | 6 mm <sup>2</sup>         |
| Weight             | 261 g                     |
| Min. cross section | 0.5 mm <sup>2</sup>       |
| Max. cross section | 6 mm <sup>2</sup>         |

#### Environmental Product Compliance

|                           |                                                                                                               |
|---------------------------|---------------------------------------------------------------------------------------------------------------|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---------------------------------------------------------------------------------------------------------------|

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 21043811 |
| eCl@ss 4.0    | 21040300 |

## Crimping pliers - CRIMPFOX ZA 2 - 1201853

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.1 | 21040300 |
| eCl@ss 5.0 | 21040300 |
| eCl@ss 5.1 | 21040300 |
| eCl@ss 6.0 | 21043800 |
| eCl@ss 7.0 | 21043811 |
| eCl@ss 8.0 | 21043811 |
| eCl@ss 9.0 | 21043811 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001186 |
| ETIM 3.0 | EC001186 |
| ETIM 4.0 | EC001186 |
| ETIM 5.0 | EC000168 |
| ETIM 6.0 | EC000168 |
| ETIM 7.0 | EC000168 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 27112118 |
| UNSPSC 7.0901 | 27111518 |
| UNSPSC 11     | 23171604 |
| UNSPSC 12.01  | 27111518 |
| UNSPSC 13.2   | 27111518 |
| UNSPSC 18.0   | 27111518 |
| UNSPSC 19.0   | 27111518 |
| UNSPSC 20.0   | 27111518 |
| UNSPSC 21.0   | 27111518 |

### Approvals

#### Approvals

---

Approvals

EAC

---

Ex Approvals

---

#### Approval details

## Crimping pliers - CRIMPFOX ZA 2 - 1201853

### Approvals

EAC



RU x-  
DE.xx08.B.02974

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1201853](#)