

## Warning label - WS 3- 5 - 0805357

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Warning plate, with 2 plastic screws, across 3 terminal blocks, pitch 5 mm



### Your advantages

- ✓ The warning labels are secured in the bridge shafts of the UK ... modular terminal blocks using plastic screws
- ✓ Mains terminal blocks are reliably covered and marked using warning labels
- ✓ Accidental actuation of the terminal points is therefore prevented

**RoHS**

### Key Commercial Data

|              |                                                                                      |
|--------------|--------------------------------------------------------------------------------------|
| Packing unit | 10 pc                                                                                |
| GTIN         |  |
| GTIN         | 4017918145149                                                                        |

### Technical data

#### Dimensions

|            |         |
|------------|---------|
| Width (a)  | 15.4 mm |
| Height (c) | 21 mm   |
| Diameter   | 0.00 mm |

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -15 °C ... 65 °C |
|---------------------------------|------------------|

#### General

|                       |                                        |
|-----------------------|----------------------------------------|
| Color                 | yellow/black                           |
| Type                  | Rectangle                              |
| Material              | PVC                                    |
| Wipe resistance       | DIN EN 61010-1 (VDE 0411-1)            |
| Printing              | Lightning flash and warning in English |
| Marking mounting type | screw, rivet                           |

## Warning label - WS 3- 5 - 0805357

### Technical data

#### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 40200202 |
| eCl@ss 4.0    | 40200100 |
| eCl@ss 4.1    | 40200100 |
| eCl@ss 5.0    | 40200100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 40200100 |
| eCl@ss 7.0    | 40200103 |
| eCl@ss 8.0    | 40200202 |
| eCl@ss 9.0    | 40200202 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001777 |
| ETIM 6.0 | EC001777 |
| ETIM 7.0 | EC001777 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 55121718 |
| UNSPSC 18.0   | 55121718 |
| UNSPSC 19.0   | 55121718 |
| UNSPSC 20.0   | 55121718 |
| UNSPSC 21.0   | 55121718 |

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0805357