

DIN rail, unperforated - NS 15 ZN UNPERF 3000MM - 1207268

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail, unperforated, Standard profile, width: 15 mm, height: 5.5 mm, acc. to EN 60715, material: Steel, galvanized, length: 3000 mm, color: silver

The figure shows a similar product

RoHS

Key Commercial Data

Packing unit	5 pc
GTIN	 4 017918 208530
GTIN	4017918208530

Technical data

Dimensions

Height	5.5 mm
Length	3000 mm
Width	15 mm
Hole width	0.00 mm
Hole height	0.00 mm
Drill hole spacing	0.00 mm

General

Material	Steel
Coating	galvanized
Color	silver


Standards and Regulations

Test standard	acc. to EN 60715
---------------	------------------

Drawings

DIN rail, unperforated - NS 15 ZN UNPERF 3000MM - 1207268

Dimensional drawing



Classifications

eCl@ss

eCl@ss 10.0.1	27400602
eCl@ss 4.0	27110800
eCl@ss 4.1	27110800
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27400600
eCl@ss 7.0	27400602
eCl@ss 8.0	27400602
eCl@ss 9.0	27400602

DIN rail, unperforated - NS 15 ZN UNPERF 3000MM - 1207268

Classifications

ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212
ETIM 6.0	EC001285
ETIM 7.0	EC001285

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708
UNSPSC 18.0	39121708
UNSPSC 19.0	39121708
UNSPSC 20.0	39121708
UNSPSC 21.0	39121708

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1207268